

E-Z-CK-DIEKIT New Generation 3-in-1 Die Kit

Thomas & Betts is proud to introduce its "NEW GENERATION", 3 in 1 E-Z-CK-DIEKIT.

This new kit is complete with 15 dies and has been created to "EZ" you into all your crimping and grounding die requirements. This new kit includes 15 die sets and has been created for all types of connections: copper conductors to copper connectors, copper conductors to aluminum connectors, aluminum conductors to aluminum connectors and finally, all our E-Z-GROUND® compression connections. This Thomas & Betts kit is the most complete!

No other manufacturer offers you all these options. Some tool manufacturers don't offer grounding dies. Some connector manufacturers offer one type of dies for copper conductors and other types of dies for aluminum conductors. No one puts it all together like T&B! This E-Z-CK-DIEKIT covers a wide range of conductor types and sizes. From #2 AWG thru 750 kcmil copper conductors and from #2 AWG aluminum conductors up to 650 kcmil. All dies listed on reverse side of this flyer can be used with Thomas & Betts 12, 14 and 15 ton crimping tools.

Similar to its predecessor, this kit comes complete with a two sided metal carrying case with everything in one convenient location. Cable vs die reference chart inside each cover lets you sort and organize all your Color-Keyed® and grounding compression dies for both copper and aluminum conductors. Additional compartments for cutting dies and adaptors round off this great package.

The total resale value of this E-Z-CK-DIEKIT is \$2700.00 and is now available at the low price of \$1290.00.

In addition and while quantities last, each purchase of this E-Z-CK-DIEKIT will get you this T&B Canada 2010 cap.

**FREE
HAT!**



Thomas & Betts

E-Z-CK-DIEKIT New Generation 3-in-1 Die Kit

E-Z-CK-DIEKIT includes:

Die Cat. No.	Qty	Die Color	Copper	Aluminum
15528	1	Brown	2 awg	n/a
15513-CK	1	Green	1 awg	4 awg
15508	1	Pink	1/0 awg	2 awg
15526	1	Black	2/0 awg	n/a
15530	1	Orange	3/0 awg	n/a
15511	1	Purple	4/0 awg	n/a
15510-CK	1	Yellow	250 kcmil	n/a
15534	1	White	300 kcmil	4/0 awg
15514-CK	1	Red	350 kcmil	250 kcmil
15506	1	Brown	500 kcmil	350 kcmil
15515-CK	1	Black	750 kcmil	650 kcmil

Thomas & Betts crimping dies for Color-Keyed® lugs and splices are designed with a flash free hexagonal configuration assorted to most of our standard connector applications. A variation of these compression dies is also offered for specific connector shapes and certain types of Thomas & Betts E-Z-GROUND® connectors, i.e.: "C" taps, "H" taps and figure 6 and 8 connectors.

Our E-Z-GROUND® round die design is the perfect choice to perform all of Thomas & Betts grounding connection options using only the 4 dies sets below and making this great offer a true 3-in-1 die kit for all your electrical compression needs!

Grounding:

Die Cat. No.	Qty	Description
15G121R	1	E-Z-GROUND®
15G86R	1	E-Z-GROUND®
15501A	1	E-Z-GROUND®
15G126R	1	E-Z-GROUND®
CTB8	1	Contax 8 oz.
COLCHA2-E	1	Connector Selector
GRNDIESEL-E	1	Ground Chart