



- Z-Channel Design Allows Cables to Pass Through Easy Routing
- Quick and Easy Assembly
- Separates and Organizes Cable
- Minimal Packaging Reduces Construction Site Waste

FEATURES

- Rugged construction; Z-frame withstands abuse
- Universal hole pattern on rack uprights mates with other rack/channel models

SPECIFICATIONS

- Channel material:
 - Z-channel: 14ga cold rolled steel
 - C-channel: 16ga cold rolled steel
- Cover material: 16ga cold rolled steel
- Finish: Durable black or aluminum color powder coat

APPROVALS/INSTALLATION

- U.S. Patent No. 6,347,714
- UL Listed File No. E129878
- Packaged to meet Telcordia® GR-63-CORE transportation requirements

APPLICATIONS

■ Use in data centers, the equipment room and telecommunications room to provide racking, cable management, grounding and power distribution for network hardware.

Telcordia® is a registered trademark of Telcordia Technologies, Inc.



Vertical Cable Management

SteadFast gates

Ensure proper bend radius

Cable management


Organize cable by groups and bundles

Front covers

Conceal cables and easily snap in place

Optional hinged covers Swing both left and right





Z-Channel Vertical



C-Channel Vertical Organizer

NEXTFRAME® Vertical Cable Channels are the most durable and easy-to-use channels ever developed.

Hubbell's innovative design incorporates many patented, labor-saving features that speed assembly and simplify maintenance. Unparalleled durability ensures long-lasting reliability.

Most important, **NEXTFRAME** Vertical Cable Channels protect cable by maintaining the proper bend radius of cables entering and exiting the organizer ensuring maximum cable transmission performance.

CABLE MANAGEMEN

VERTICAL ORGANIZERS

Z-Channel, 6" with Cover

Contents:

VS76(A): 2 Z-channels 38.5" H x 6" W x 10.5" D

2 covers 38.5" W x 6" W

VS86(A): 1 Z-channel and 1 cover for:

lower, 45.38" H x 6" W x 10.5" D

upper, 38.5" H x 6" W

4 gates 24 spools

4 1/2"-13 x 1" bolts with nuts and washers

Rack Height Inches (mm)	Catalog No.
7' (2134) or 7.5' (2286)	VS76*
8' (2438)	VS86*

VS46*

VS73*

Z-Channel, 6" (for Short Racks)

Contents:

1 Z-channel 38.5" H x 6" W x 10.5" D

16 spools

2 1/2"-13 x 1" bolts with nuts and washers

4' (1219) and 5.5' (1676)

Z-Channel, 41/2" Wide, 0.25" Diameter

Contents:

2 Z-channels, 38.50" x 4.5" x 10.5"

24 spools

4 1/2"-13 x 1" bolts with nuts and washers

7' (2134) **VS74**

C-Channel, 31/4" Wide

2 C-channels 38.5" H x 3.25" W x 10.5" D

24 spools

4 1/2"-13 x 1" bolts with nuts and washers

7' (2134)

*Product is Black. Add "A" at end of Catalog No. for Aluminum.

VERTICAL ORGANIZERS WITH HINGED COVERS

Contents:

2 Z-channels 38.5" H x 12.5" D

2 38.5" covers

4 hinges and gates

24 spools

4 1/2"-13 x 1" bolts with nuts and washers

Black	7' (2134)	VS76H	VS74H	VS73H	
Color	Rack Heigh In. (mm) t	6" Wide Catalog No.	4½" Wide Catalog No.	31/4" Wide Catalog No.	

COVERS

Contents: 1 cover

Cover Width 38.5" H Black Black Catalog No. 45.38" H Aluminum Catalog No. 45.38" H Aluminum Catalog No. 3" VSC3* VSC3L VSC3LA 4" VSC4 VSC4L VSC4LA
Cover Black Black Aluminum Width Catalog No. Catalog No. Catalog No.
Cover Black Black Aluminum

^{*}Add "A" at end of Catalog Number for Aluminum.

HINGE KIT

Contents:

2 hinges and fasteners



Color	Catalog No.
Black	VCKH

Note: Gates not provided; order separately. Can be used to convert VS76 to VS76H.

JOINING KIT

Contents:

VS46

1 joining plate

4 #12-24 x 5/8" screws, nuts, washers

 $4 \frac{1}{2}$ "-13 x 1" bolts w/ nuts and washers




VERTICAL RINGS

Contents:

2 vertical rings

1 mounting kit



	IVIOOVIVII 12 IVIOOVIVII 122
Description	Catalog No.
Bracket, one side	MCCVMR2
Bracket, between racks	MCCVMR22

CABLE MANAGEMENT SPOOLS




Catalog No.	
ICKSS	
ICKSS6	
ICKSS9	

GATES

Contents:

1 kit of 16 gates







www.hubbell-premise.com

VSC6

