


[PRODUCTS \(/PRODUCTS\)](#)
[SUPPORT](#)
[INNOVATIONS \(/INNOVATIONS\)](#)

[SIGN UP / LOG IN](#)

[View More +](#)
[2475-20](#)
[2475-21XC](#)
[\(/Products/Power-Tools/Specialty-Tools/2475-20\)](#)

M12™ Compact Inflator kit

No Reviews Write the First Review (https://www.milwaukeeetool.com/write-review/?pr_page_id=2475-21XC&pr_merchant_id=375152&pr_api_key=dd031606-9334-476a-906e-368515eead9&pr_merchant_group_id=14854)

FASTEST CORDLESS TIRE INFLATOR. The Milwaukee® M12™ Compact Inflator delivers fast, accurate, easy inflation with the portability to take anywhere. With the capability to complete demanding applications like car, LT truck, and compact equipment tires, the M12™ Compact Inflator gives users ultimate power and efficiency. Rated to deliver over 120PSI, The high efficiency motor and pump top-off car tires in under 1 minute. The TrueFill™ Auto shut-off technology delivers highly accurate pressure, protects from overfill, and automatically senses speed of fill to deliver precise shut-off at the desired PSI. Additionally, the unit includes a large easy to read back-

Read More

INCLUDES:

(1) M12™ Compact Inflator (2475-20) ([/Products/Power-Tools/Specialty-Tools/2475-20](#))

(1) M12™ REDLITHIUM™ XC 4.0 Extended Capacity Battery Pack (48-11-2440) ([/Products/Batteries-and-Chargers/M12-Batteries-and-Chargers/48-11-2440](#))

(1) M12™ Lithium-ion Battery Charger (48-59-2401) ([/Products/Batteries-and-Chargers/M12-Batteries-and-Chargers/48-59-2401](#))

(1) Ball Inflation Needle

Read More

Where To Buy

KEY FEATURES

Fastest Cordless Tire Inflator: Top-off a car tire in under 1 minute. (28 - 35 PSI)

SPECIFICATIONS

REVIEWS

Inflates car, LT truck, and compact equipment tires.

REDLINK™ Intelligence: TrueFill™ Auto Shut-off technology increases accuracy, protects from over-temp and over-fill.

High efficiency pump and motor for true 120 PSI capability.

Illuminated digital gauge with target and current pressure reading.

Fills a LT truck tire in under 4 minutes (30-45 psi).

Compact, portable, and easy-to-store in any car or truck.

Weather and impact resistant with a reinforced cage.

Anti-vibration feet for no tool movement while running.

3-year limited warranty.

BATTERY SPECIFICATIONS

Voltage 12V

PRODUCT SPECIFICATIONS

Length 6.50"

Weight 3.83"

Power Source Corded

Width 6.50 lbs

0 88 CFM 0 PSI

0 63 CFM 35 PSI

PSI Rating 0 -120 PSI

Hose Length 26"

Gauge Accuracy +/- 3%

Duty Cycle 50%

Height 7.50"

Write the First Review (https://www.milwaukeeetool.com/write-review/?pr_page_id=2475-21XC&pr_merchant_id=375152&pr_api_key=dd031606-9334-476a-906e-368515eeaad9&pr_merchant_group_id=14854)

SIGN ME UP!

Be the first to know about special offers, new product launches and events.

Email Address*

Trade*

Select a Trade

Zip Code*

Subscribe

(https://www.milwaukeetool.com/Products/Power-Tools/Specialty-Tools/2475-21XC)

PRODUCTS

Power Tools (/Products/Power-Tools)

Lighting (/Products/Lighting)

Hand Tools (/Products/Hand-Tools)

Storage (/Products/Storage-Solutions)

Work Gear (/Products/Work-Gear)

Instruments (/Products/Instruments)

Accessories (/Products/Accessories)

ABOUT US

Milwaukee Story (/Company/Milwaukee-Story)

Press Releases (/News/Press-Releases)

Milwaukee Swag (https://www.milwaukeetoolswag.com)

Careers (https://www.milwaukeetool.jobs/)

Contact Us (/Contact)



US : : EN - Change Site / Language (/Country-Selector)



Where to Buy Milwaukee Products (/Buy-Now)

NEW PRODUCTS

M18 FUEL™ High Torque ½” Impact Wrench with Pin Detent - 2766-20 (/Products/Power-Tools/Fastening/Impact-Wrenches/2766-20)

M18 FUEL™ Drain Snake w/ CABLE DRIVE™ - 2772A-20 (/Products/Power-Tools/Drain-Cleaning/Sink-Machines/2772A-20)

M18™ RADIUS™ Site Light/Charger w/ ONE-KEY™ - 2150-20 (/Products/Lighting/Site-Lights/2150-20)

PACKOUT™ Rolling Tool Box - 48-22-8426 (/Products/Storage-Solutions/PACKOUT/PACKOUT-Tool-Boxes/48-22-8426)

SHOCKWAVE Linemans Impact Auger Bits (/Products/Accessories/Metal-Drilling/Wood-Boring-Bits/SHOCKWAVE Linemans Impact Auger Bits)

HOW CAN WE HELP?

Contact Us (/Contact)

eService Repair (/eService)

Find A Service Center (/Support/Find-A-Service-Center)

Manuals and Downloads (/Support/Manuals-and-Downloads)

Work At Milwaukee (https://www.milwaukeetool.jobs/)