



# TRACJACK

Faceplates and Plate Mountings

## OR-403STJ Double Gang Stainless Steel TracJack Faceplates



OR-403STJ28



OR-403STJ212

## Double Gang Stainless Steel TracJack Faceplates

PART NO.	DESCRIPTION
OR-403STJ28	Holds (8) TracJacks, 4.5" x 4.5"
OR-403STJ212	Holds (12) TracJacks, 4.5" x 4.5"

## TracJack Frames and Cover Plates

Legrand® offers TracJack® mountings in both the 106-Type duplex footprint or the Stylistics® rectangular (GFCI) footprint, with a variety of port capacities to match your workstation applications. These two footprints are common to Wiremold® and many other industry standard raceway, furniture, pedestals and floor boxes. Legrand also offers plastic cover plates with recessed label fields and slotted screw holes to adjust alignment. All parts are ruggedly constructed from high impact thermo-plastic 94V-0 rated to ensure long life.

## OR-408000 106-Type TracJack Frames



OR-40800017



OR-40800018



OR-40800019

## 106-Type TracJack Frames

PART NO.	DESCRIPTION
OR-40800017*	Holds (2) TracJacks
OR-40800018	Holds (3) TracJacks
OR-40800019*	Holds (4) TracJacks

Notes: Standard color is fog white.  
\* Indicates also available in -99 Wiremold ivory and -88 white.

## OR-40300 106-Type Plastic Cover Plates



OR-40300255



OR-40300256

## 106-Type Plastic Cover Plates

PART NO.	DESCRIPTION
OR-40300255	Single gang cover, 2.75" x 4.5"
OR-40300256	Double gang cover, 4.5" x 4.5"

Notes: Standard color for 106-Type Cover Plate is fog white. For other colors, contact sales.

## OR-419000 Stylistics TracJack Frames



OR-41900017



OR-41900018

## Stylistics TracJack Frames

PART NO.	DESCRIPTION
OR-41900017*	Single gang cover, 2.75" x 4.5"
OR-41900018*	Double gang cover, 4.5" x 4.5"

Notes: Standard color is fog white.  
\* Indicates also available in -99 Wiremold ivory

# TRACJACK

Plates and Undercover Wall Plate

## OR-403005

Stylistics Plastic Cover Plates



OR-40300270



OR-40300271

## OR-403STJ1WP

Single Gang Stainless Steel TracJack Faceplates with Phone Studs



OR-403STJ1WP

## Stylistics Plastic Cover Plates

PART NO.	DESCRIPTION
OR-40300270	Single gang cover, 2.75" x 4.5"
OR-40300271	Double gang cover, 4.5" x 4.5"

Notes: Standard color for Stylistics® cover plates is fog white. Contact Legrand sales department for other colors

## Single Gang Stainless Steel TracJack Faceplates with Phone Studs

PART NO.	DESCRIPTION
OR-403STJ1WP	Holds (1) TracJack, 2.75" x 4.5"

Notes: Not compatible with 2554 series wall phones.

## TracJack Surface Mount Boxes

Legrand® TracJack® surface mount boxes are available to house from two to six TracJacks. Bases are easily installed with supplied screws or double-sided adhesive. Snap-on covers have recessed label fields. Boxes are ruggedly constructed from high impact thermo-plastic 94V-0 rated. Standard color is fog white. Compatible with Wiremold® 2700, 2800 and 2900 raceway series.

## OR-403005

Surface Housings for TracJack



OR-404TJ2



OR-404TJ4



OR-404TJ6

## Surface Housings for TracJack

PART NO.	DESCRIPTION
OR-404TJ2	Holds (2) TracJacks, 2.59" x 2.27" x 1.20"
OR-404TJ4*	Holds (4) TracJacks, 4.80" x 3.6" x 1.16"
OR-404TJ2X2	Holds (4) TracJacks, jacks exit from both sides, 4.0" x 2.42" x 1.16"
OR-404TJ6**	Holds (6) TracJacks, 6.98" x 4.33" x 1.16"

Notes: \*Can mount directly to single gang recessed wall boxes. Includes one TracJack blank.

\*\*Includes internal storage ring for fiber and two TracJack blanks. Can mount directly to single or double gang recessed wall boxes.

Contact Legrand sales department for other colors

# TRACJACK

## Furniture Bezels

### Furniture Bezels

Legrand® offers TracJack® plates for most furniture systems. Plates easily snap mount into furniture, requiring no special tools. Plates are ruggedly constructed from high impact thermo-plastic 94V-0 rated.

IMPORTANT: Measure furniture openings to determine the correct plate.

### OR-40300, OR-421000, OR-407000 Furniture Plates for TracJack



### Furniture Plates for TracJack

PART NO.	DESCRIPTION
OR-40300577	Holds (4) TracJacks, fits Herman Miller Beltline furniture openings 2.35" x 3.41" (+.015) for .125" thick material, fog white
OR-40300577-00	Black
OR-40300576	Holds (6) TracJacks, fits Herman Miller Beltline furniture openings 2.35" x 3.41" (+.015) for .125" thick material, fog white
OR-40300576-00	Black
OR-40300575	Holds (6) TracJacks, fits Herman Miller Baseline furniture openings 1.89" x 2.99" (+.015) for .063" thick material, fog white
OR-40300575-00	Black
OR-40300633*	Holds (4) TracJacks, two-piece base and cover, adjustable to fit a range of common furniture openings 2.67"-2.75" x 1.34"-1.41" for .065" thick material, fog white
OR-40300633-00*	Black
OR-42100009	Adapter plate, front-loads (3) TracJacks, fog white
OR-42100009-00	Black
OR-42100054	Adapter plate, rear-loads (3) TracJacks, fog white, 5pk
OR-42100054-00	Black, 5pk
OR-40700071	.125"D bezel mounts adapter plates above to 2.71" x 1.38" (+.035) opening, fog white
OR-40700071-00	Black
OR-40700072*	.625"D bezel mounts adapter plates above to 2.71" x 1.38" (+.035) opening, fog white
OR-40700072-00*	Black
OR-40700073*	1.0"D bezel mounts adapter plates above to 2.71" x 1.38" (+.035) opening, fog white
OR-40700073-00*	Black

Notes: \*Have recessed label fields.