PHANTON

KD-HDFIX22

HDMI Extender, Booster & Buffer of EDID with built-in Audio De-Embedder of Digital Coaxial & Analog L/R, supports HDCP 2.2, TMDS, HPD, Ultra HD/4K

Key Features

- **Extension:** Capable of extending UHD/4K and 1080p resolution up to 75 ft. / 23 m. in and 75 ft. / 23 m. out (150 ft. / 46 m. total)
- > HDMI Correction: Resolves common HDMI integration obstacles such as HDCP, EDID, HPD, and audio breakout
- Resolution Support: Supports all SD, HD, and VESA resolutions up to Ultra HD/4K, 3D and 1080p/60 (60Hz & 50Hz)
- > 4K/Ultra HD: Support for 4096x2160 or 3840x2160 24/25/30Hz at 4:4:4 or 60Hz at 4:2:0.
- > HDCP 2.2: Compliancy up to HDCP 2.2
- > 3D Ready: Capability to pass 3D stereoscopic signal formats
- > Full Buffer System™: Manages TMDS re-clocking / signal re-generation, HDCP authentication to source & display, and EDID Control handshake
- Audio De-Embedding: Audio from the HDMI input is de-embedded through the Coax digital (PCM) and/or Analog L/R audio output
- Auto-EQ: Precise signal equalization applied to input and output signals automatically delivers best possible picture quality
- > EDID Control: 15 internal EDID tables or EDID copy from output/display
- > Forced HPD: Enables integrator to choose if active signal voltage is forced to connected input device
- > Licensing: Fully licensed and compatible with all HDMI and HDCP technologies
- > I2C Communication: EDID and HDCP authentication to Display and Source
- > RS-232 Controllable: Control of unit and connectivity status
- CEC Support: For inter-device control between main input and output HDMI channel
- **Deep Color Support:** Up to 16 bits/color at 1080p/60



Specifications

- » HDMI Connector: Type A 19 Pin Female
- » Advanced HDMI features: Ultra HD/4K, 3D
- » Audio: Supports DTS-HD, Dolby True HD and 2 CH PCM
- » External Analog Audio: supports 2 Channel PCM audio only, NO Multi-Channel, PCM, Dolby, DTS or HD audio support
- » HDMI Video/Audio signal: 1.2V p-p
- » DDC Signal: 5V p-p (TTL)
- » Regulation: CE, RoHS, WEEE
- » Power Supply: KD-PS5V1A, 5V/1A, 100-240VAC, 50-60Hz, Interchangeable head
- » Product Dimensions: 3.6" x 2.5" x 1", Weight: 4 oz
- » Shipping Dimensions: 6.3" x 4.2" x 3.3", Weight: 16 oz
- » Enclosure: Black Metal



System Design Example

