TRAC-LITES LOW VOLTAGE SERIES R701, R702, R731 and R740

REV-4/11

PRODUCT DESCRIPTION

Socket Ceramic Bi-Pin.

Transformer 50VA 12V electronic transformer with circuit protection.

Aiming 90° vertical aiming capability and 358° rotation.

Adapter Copper alloy contacts provide precise spring action • True, positive electrical ground • Spring-loaded locking latch with embossed polarity arrows secures trac light to trac • Compatible with both Trac-Lites and Trac-Master Trac • "Pull-up" contact to up position for use on Trac-Master two-circuit trac.

Labels UL/CUL listed.

Product specifications subject to change without notice.

Low Voltage MR16 Cylinder

Construction Polycarbonate transformer housing with a painted formed steel lamp housing.

Catalog Number	Finish	Lamp
R701WH	White	12V, 20-50W MR16
R701BL	Black	12V, 20-50W MR16

ACCESSORIES

Cat. No.	Description	Cat. No.	Description	Cat. No.	Description
T741-6	Color Filters/Lenses	T7477	Prismatic Spread Lens	T7478	Linear Spread Lens
T7401-18	Dichroic Lenses	T7420	Diffuse Spread Lens	T7421	Uniformity Lens
T7422	UV Filter Lens	T7459BL	Hexcell Louver		
See specification	sheet D1 2 2 for detail	\$			


Low Voltage MR16 Roundback

Construction Polycarbonate transformer housing with a painted formed steel lamp housing.

Catalog Number	Finish	Lamp
R702WH	White	12V, 20-50W MR16
R702BL	Black	12V, 20-50W MR16
R702BZ	Painted Bronze	12V, 20-50W MR16

ACCESSORIES

Cat. No.	Description	Cat. No.	Description	Cat. No.	Description
T551-5	Color Filters	T557	Prismatic Spread Lens	T559	Linear Spread Lens
T5501-18	Dichroic Lenses	T5520	Diffuse Spread Lens	T5521	Uniformity Lens
T5522	UV Filter Lens	T5559BL	Hexcell Louver		
See specification sheet D1.2.2 for details.					







Project:

Fixture Type:

Location:

Contact/Phone:



TRAC-LITES LOW VOLTAGE SERIES R701, R702, R731 and R740

Low Voltage MR16 Gimbal Ring

Construction Polycarbonate transformer housing with a painted formed steel lamp housing.

Catalog Number	Finish	Lamp
R731WH	White	12V, 20-50W MR16
R731BL	Black	12V, 20-50W MR16
R731SL	Silver	12V, 20-50W MR16
R731BZ	Painted Bronze	12V, 20-50W MR16

ACCESSORIES

Cat. No.	Description	Cat. No.	Description	Cat. No.	Description
T741-6	Color Filters/Lenses	T7477	Prismatic Spread Lens	T7478	Linear Spread Lens
T7401-18	Dichroic Lenses	T7420	Diffuse Spread Lens	T7421	Uniformity Lens
T7422	UV Filter Lens	T7459BL	Hexcell Louver		
See specification sheet D1.2.2 for details.					



Low Voltage MR16 Pinchback

Construction Polycarbonate transformer housing with a painted die-cast aluminum lamp housing.

Catalog Number	Finish	Lamp
R740WH	White	12V, 20-50W MR16
R740BL	Black	12V, 20-50W MR16
R740SL	Silver	12V, 20-50W MR16
R740BZ	Painted Bronze	12V, 20-50W MR16

ACCESSORIES	
ACCESSORIES	

Cat. No.	Description	Cat. No.	Description	Cat. No.	Description
T741-6	Color Filters/Lenses	T7477	Prismatic Spread Lens	T7478	Linear Spread Lens
T7401-18	Dichroic Lenses	T7420	Diffuse Spread Lens	T7421	Uniformity Lens
T7422	UV Filter Lens	T7459BL	Hexcell Louver		
See specification sheet D1.2.2 for details.					



