

# MPD15-11C



MPD15-11C Double Pushbutton



## General Information

|                       |  |
|-----------------------|--|
| Extended Product Type | MPD15-11C  |
| Product ID            | 1SFA611144R1108  |
| EAN                   | 7320500280904  |
| Catalog Description   | MPD15-11C Double Pushbutton  |
| Long Description      | Modular Double Pushbutton - Momentary - Flush/Extended - Green/Red Actuator, Clear Indicator - Illuminated - No contact block - Lower Button: STOP - Upper Button: START |

## Ordering

|                        |               |
|------------------------|---------------|
| EAN                    | 7320500280904 |
| Minimum Order Quantity | 10 piece      |
| Customs Tariff Number  | 8536501999    |

## Dimensions

|                            |          |
|----------------------------|----------|
| Product Net Width          | 0.054 m  |
| Product Net Height         | 0.03 m   |
| Product Net Depth / Length | 0.043 m  |
| Product Net Weight         | 0.025 kg |

## Container Information

|                                |               |
|--------------------------------|---------------|
| Package Level 1 Units          | 1 piece       |
| Package Level 1 Width          | 0.11 m        |
| Package Level 1 Height         | 0.03 m        |
| Package Level 1 Depth / Length | 0.15 m        |
| Package Level 1 Gross Weight   | 0.025 kg      |
| Package Level 1 EAN            | 7320500280904 |

## Environmental

|                         |   |
|-------------------------|---|
| Ambient Air Temperature | Storage -30 ... +85 °C<br>Operation -25 ... +70 °C              |
| RoHS Status             | Following EU Directive 2002/95/EC August 18, 2005 and amendment |

## Additional Information

|                       |                                     |
|-----------------------|-------------------------------------|
| Actuator Type         | Flush/Extended                      |
| Bezel Material        | Black plastic                       |
| Block                 | No contact block                    |
| Color                 | Green/Red Actuator, Clear Indicator |
| Degree of Protection  | Front IP66<br>Terminals IP20        |
| Function              | Momentary                           |
| Illumination          | Illuminated                         |
| Lower Button Color    | Red                                 |
| Lower Button Text     | STOP                                |
| Mechanical Durability | 2 million                           |
| Product Main Type     | MPD15                               |
| Product Name          | Double Pushbutton                   |
| Product Range         | Modular                             |
| Product Type          | MPD                                 |
| RoHS Date             | 0635 4                              |
| Symbol / Text         | START/STOP                          |
| Upper Button Color    | Green                               |
| Upper Button Text     | START                               |

## Certificates and Declarations (Document Number)

|                                   |                 |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | 1SFC151005C0201 |
| Declaration of Conformity - CE    | 1SFA1-83        |
| Environmental Information         | 1SFC151010D0201 |
| Instructions and Manuals          | 1SFC151005C0201 |
| RoHS Information                  | 1SFC151011D0203 |

## Classifications

|                            |  |
|----------------------------|--|
| ETIM 4                     | EC002024 - Accessories for control circuit devices |
| ETIM 5                     | EC000221 - Front element for push button           |
| ETIM 6                     | EC000221 - Front element for push button           |
| ETIM 7                     | EC000221 - Front element for push button           |
| Object Classification Code | S  |
| UNSPSC                     | 39121512   |

## Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Modular Plastic Range

