

## Maestro Wireless® Dimmers and Switches


The Maestro Wireless® solution incorporates Maestro Wireless® load controls, wireless sensors, and wireless remote controls, which provide a system that delivers energy savings, convenience, and ease of installation.

Maestro Wireless® dimmers and switches use Lutron® patented Clear Connect® RF Technology, which enables wireless communication with Radio Powr Savr™ sensors and Pico® wireless controls for light control and general switched loads.


### Features

- The Maestro Wireless® solution provides dimming/switching of multiple load types, occupancy/vacancy sensing, daylight harvesting, and high-end trim.
- Lutron® patented Clear Connect® RF Technology works through walls and floors.
- Incorporates advanced features such as fade ON/fade OFF, high-end trim, and rapid full-ON.
- Controls include Front Accessible Service Switch (FASS™) for safe lamp replacement.
- Two-wire dimmers and switches available for retrofit applications.
- Power failure memory: If power is interrupted, the control will return to its previously set level prior to interruption.


### Receiving Devices Maestro Wireless® Controls




Neutral and Non-Neutral Dimmers



Neutral and Non-Neutral Switches




Lamp Dimmers




Plug-In Modules


### Transmitting Devices Radio Powr Savr™ Sensors



Ceiling-Mounted Occupancy and Vacancy Sensors




Wall-Mounted Occupancy and Vacancy Sensors



Daylight Sensors

### Pico® Wireless Controls



Job Name:

Model Numbers:

Job Number:

## Maestro Wireless® Dimmers

### Models Available

#### Dimmers

#### CFL/LED/Halogen/Incandescent/Magnetic Low-Voltage

MRF2-6CL-XX	150 W CFL/LED Dimmer; 600 W/600 VA Incandescent/MLV Dimmer 120 V~
MRF2-6MLV-XX	600 W/600 VA Incandescent/MLV Dimmer 120 V~
MRF2-6ND-120-XX*	600 W/600 VA Spec-Grade Neutral wire Dimmer 120 V~
MRF2-10D-120-XX	1000 W/1000 VA Spec-Grade Dimmer 120 V~

#### 3-Wire Fluorescent

MRF2-F6AN-DV-XX*	6 A 3-wire Fluorescent Spec-Grade Neutral-Wire Dimmer 120–277 V~
------------------	---

#### Electronic Low-Voltage Dimmer

MRF2-6ELV-120-XX*	600 W ELV Dimmer 120 V~
-------------------	-------------------------

\* Neutral wire required

### Companion Dimmers

#### Claro® Gloss Finishes

MA-R-XX	Companion Dimmer 120 V~
MA-R-277-XX	Companion Dimmer 277 V~

#### Satin Colors® Satin Finishes

MSC-AD-XX	Companion Dimmer 120 V~
MSC-AD-277-XX	Companion Dimmer 277 V~

"XX" in the model number represents color/finish code.

Dimmer



Companion Dimmer



Job Name:	Model Numbers:
Job Number:	