

## Downlights

	<p><b>Catalog #</b> 24W-WH 24B-WH 24B-ABZ 24B-SC</p>	<p><b>Description</b> White Baffle, White Trim Black Baffle, White Trim Black Baffle, Classic Aged Bronze Trim Black Baffle, Satin Chrome Trim</p>	<p><b>Max. Lamp Rating</b> IC2/TC2/TC2R: 75W PAR30L, 65W BR30 <b>Aperture</b> 5 3/4"</p>	<p><b>Tapered Baffle</b></p>
	<p><b>Catalog #</b> 25W-WH 25B-WH 25B-SC</p>	<p><b>Description</b> White Baffle, White Trim Black Baffle, White Trim Black Baffle, Satin Chrome Trim</p>	<p><b>Max. Lamp Rating</b> IC2: 85W BR40/90W PAR38 TC2/TC2R: 120W BR40/150 PAR38 <b>Aperture</b> 5 3/4"</p>	<p><b>Straight Baffle</b></p>
	<p><b>Catalog #</b> 28W-WH 28B-WH</p>	<p><b>Description</b> White Baffle, White Trim Black Baffle, White Trim</p>	<p><b>Max. Lamp Rating</b> IC2: 75W A19/100W PAR38, 75W PAR30/30L, 85W BR30, 120W BR40 TC2/TC2R: 150W A21/150W PAR38, 75W PAR30/30L, 85W BR30, 120W BR40 <b>Aperture</b> 5 7/8"</p> <p><b>AIR-LOC</b> </p>	<p><b>Ultra-Trim Baffle - Fully Enclosed</b></p>
	<p><b>Catalog #</b> 244W-WH 244B-WH</p>	<p><b>Description</b> White Baffle, White Trim Black Baffle, White Trim</p>	<p><b>Max. Lamp Rating</b> IC2/TC2/TC2R: 75W PAR30, 75W PAR30L, 65W BR30 <b>Aperture</b> 5 3/4"</p> <p><b>AIR-LOC</b></p>	<p><b>Shallow Baffle</b></p>
	<p><b>Catalog #</b> 254W-WH 254B-WH</p>	<p><b>Description</b> White, White Trim Black, White Trim</p>	<p><b>Max. Lamp Rating</b> IC2/TC2/TC2R: 75W PAR30, 100W PAR38 <b>Aperture</b> 5 5/8"</p>	<p><b>PAR30 Deep Baffle</b></p>
	<p><b>Catalog #</b> 26B-WH 26C-WH 26G-WH 26HZ-WH 26PT-SC 26W-WH 26WHZ-WH</p>	<p><b>Description</b> Black Alzak®, White Trim Clear Alzak®, White Trim Gold Alzak®, White Trim Haze, White Trim Pewter Alzak®, Satin Chrome Trim Gloss White, White Trim Wheat Haze, White Trim</p>	<p><b>Max. Lamp Rating</b> IC2: 90W PAR38/85W BR40 TC2/TC2R: 150W PAR38/120W BR40 <b>Aperture</b> 5 3/4"</p>	<p><b>Straight Cone</b></p>
	<p><b>Catalog #</b> 27B-WH 27C-WH 27G-WH 27HZ-WH 27PT-SC 27W-WH 27WHZ-ABZ 27WHZ-WH</p>	<p><b>Description</b> Black Alzak®, White Trim Clear Alzak®, White Trim Gold Alzak®, White Trim Haze, White Trim Pewter Alzak®, Satin Chrome Trim Gloss White, White Trim Wheat Haze, Classic Aged Bronze Trim Wheat Haze, White Trim</p>	<p><b>Max. Lamp Rating</b> IC2/TC2/TC2R: 75W PAR30L/65W BR30 <b>Aperture</b> 5 7/8"</p>	<p><b>Tapered Cone</b></p>