

This **MINING SERVICE** lamp was specifically designed to resist the possible harsh conditions inside a mine such as extreme heat, moisture or vibration.



Order code	Description	Watts (W)	Base	Volts (V)	Finish/Colour	Average life at 120 V (hrs)	Filament	Lumens at 120 V (lm)	Case qty
<b>R40</b>									
MOL : 6 3/4 in. (167 mm) LCL : 4 1/4 in. (108 mm)									
50482	300R40/FL/5M/MN/130V/STD	300	E26	130	Clear	5 000	CC-6	2 271	12

**PLANT LIGHTS** promote plant growth. They emit light spectrum similar to that from the sun, allowing indoor growth with outdoor conditions.



Order code	Description	Watts (W)	Base	Volts (V)	Finish/Colour	Average life (hrs)	Filament	Lumens (lm)	Case qty
<b>A19</b>									
MOL : 4 1/4 in. (108 mm) LCL : 3 1/8 in. (79 mm)									
50957	60A19/2M/PL/120V/STD	60	E26	120	Plant light	2 000	C-9	N/A	120
<b>BR30</b>									
MOL : 5 1/8 in. (130 mm) LCL : 3 11/16 in. (85 mm)									
50958	75R30/1.5M/PL/120V/STD	75	E26	120	Plant light	1 500	C-9	N/A	60
50959	100BR30/1.5M/PL/120V/STD	100	E26	120	Plant light	1 500	C-9	N/A	60
<b>BR40</b>									
MOL : 6 3/4 in. (167 mm) LCL : 4 1/4 in. (108 mm)									
14726	150BR40/2M/PL/120V/STD	150	E26	120	Plant light	2 000	C-9	N/A	60
<b>R25</b>									
MOL : 4 3/4 in. (121 mm) LCL : 3 11/16 in. (85 mm)									
50541	75R25/2M/PL/120V/STD	75	E26	120	Plant light	2 000	C-9	N/A	120

**TRAFFIC SIGNAL LAMPS** have been most commonly used in lights on roadways. Their long life of 8 000 hours and ability to stand up to vibration allows these lamps to be used in many other applications.



Order code	Description	Watts (W)	Base	Volts (V)	Finish/Colour	Average life (hrs)	Filament	Lumens (lm)	Case qty
<b>A19</b>									
MOL : 4 1/4 in. (108 mm) LCL : 2 7/8 in. (62 mm)									
10863	60A19/CL/8M/TS/K/120 125V	125	E26	120	Clear	5 000	C-9	1 200	12
<b>A21</b>									
MOL : 5 1/8 in. (135 mm) LCL : 2 7/8 in. (62 mm)									
15554	40A21/CL/8M/TS/125 130V	40	E26	125	Clear	8 000	C-11V	610	120
14620	67A21/CL/8M/TS/125 130V /2P (2 pack)	67	E26	125	Clear	8 000	C-9	610	60
10905	69A21/CL/8M/TS/125 130V /2P (2 pack)	69	E26	125	Clear	10 000	C-11V	665	120

# Mining, Plant & Traffic Lamps