

## LED STEP & WALL LIGHTS

**P6827** and **P6828** LED step/wall lights are available in a vertical or horizontal configuration for mounting into a single-gang wallbox

- cCSAus listed for wet locations
- Integral power supply module in a compact package
- Consumes less than 5w of power per fixture
- Warm white 3000K LED's included
- CRI: 84+
- Beam spread: 120 degrees



P6827-0930K



P6828-0930K



P6827-3030K




P6828-3030K

| Product No.        | Finish         | Description                     | Size         | Lamp              |
|--------------------|----------------|---------------------------------|--------------|-------------------|
| <b>P6827-0930K</b> | Brushed Nickel | Mini horizontal step/wall light | 4-13/16" W.  | 4w LED, included. |
| <b>P6827-3030K</b> | White          | Mini horizontal step/wall light | 3" ht.       |                   |
| <b>P6828-0930K</b> | Brushed Nickel | Mini vertical step/wall light   | 3" W.        | 4w LED, included. |
| <b>P6828-3030K</b> | White          | Mini vertical step/wall light   | 4-13/16" ht. |                   |

**P6829** and **P6832** LED step/wall lights provide an attractive solution for a variety of illumination tasks

- cCSAus listed for outdoor as well as indoor applications
- Integral power supply module in a compact package
- Consumes less than 4w of power per fixture
- Warm white 3000K LED's included
- CRI: 84+
- Beam spread: 120 degrees



P6829-0930K



P6829-2030K



P6829-3030K



P6829-3130K



P6832-0930K



P6832-3130K

| Product No.        | Finish         | Description                   | Size       | Lamp              |
|--------------------|----------------|-------------------------------|------------|-------------------|
| <b>P6829-0930K</b> | Brushed Nickel | Mini vertical step/wall light | 3" W.      | 4w LED, included. |
| <b>P6829-2030K</b> | Antique Bronze | Mini vertical step/wall light | 4-3/4" ht. |                   |
| <b>P6829-3030K</b> | White          |                               |            |                   |
| <b>P6829-3130K</b> | Black          |                               |            |                   |
| Product No.        | Finish         | Description                   | Size       | Lamp              |
| <b>P6832-0930K</b> | Brushed Nickel | Mini vertical step/wall light | 4-3/4" W.  | 4w LED, included. |
| <b>P6832-2030K</b> | Antique Bronze | Mini vertical step/wall light | 3" ht.     |                   |
| <b>P6832-3030K</b> | White          |                               |            |                   |
| <b>P6832-3130K</b> | Black          |                               |            |                   |

U.S. Patent #.  
6357891, 5379199