

TBQC Interposing Terminal Block

IC693ACC329	Interposing terminal block base for IC694MDL645, IC694MDL646, and IC694MDL240. The base can also be used with any 20 point terminal discrete or analog modules not listed.	Active
IC693ACC330	Interposing terminal block base for IC694MDL740 and IC694MDL742	Discontinued
IC693ACC331	Interposing terminal block base for IC694MDL741	Discontinued
IC693ACC332	Interposing terminal block base for IC694MDL940	Active
IC693ACC333	Interposing terminal block base for IC694MDL340	Active
IC693ACC337	Interposing terminal block base for IC693MDL654/655/752/753 and IC694MDL654/655/752/753	Active

TBQC Cables

IC693CBL327	Cable, Left Side, One -24 Pin 90 Degree Connector, 3 Meter. Cable has a connector on only one end and open on the other. Cable used with TBQC I/O Face Plate Adapter or Fujitsu style I/O modules.	Active
IC693CBL328	Cable, Right Side, One -24 Pin 90 Degree Connector, 3 Meter. Cable has a connector on only one end and open on the other. Cable used with TBQC I/O Face Plate Adapter or Fujitsu style I/O modules.	Active
IC693CBL329	Cable, Left Side, One -24 Pin 90 Degree Connector, 1 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Active
IC693CBL330	Cable, Right Side, One -24 Pin 90 Degree Connector, 1 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Active
IC693CBL331	Cable, Left Side, One -24 Pin 90 Degree Connector, 2 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Active
IC693CBL332	Cable, Right Side, One -24 Pin 90 Degree Connector, 2 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Active
IC693CBL333	Cable, Left Side, One -24 Pin 90 Degree Connector, 0.5 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Active
IC693CBL334	Cable, Right Side, One -24 Pin 90 Degree Connector, 0.5 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Active

High Density Terminal Block Quick Connect (32 point I/O terminals)

High Density Terminal Block Quick Connect (TBQC) for selected I/O modules enables the user to easily connect interposing terminal blocks. The HDTBQC consist of a I/O module terminal block with a 40 pin Fujitsu male connector, cable and interposing terminal block. The HDTBQC is compatible with modules that accept IC694TBC032 (24 VDC discrete inputs and analog input and output modules. The HDTBQC is not compatible with discrete output modules).

HDTBQC I/O Module Face Plate Adapter

IC694TBC032	High-density, 36-point, terminal block with cable connector. IC695ALGxxx, IC69xMDL660 and IC694MDL664 modules only. Discrete output modules not supported.	Active
-------------	---	--------

HDTBQC Interposing Terminal Block

IC694RTB032	High-density remote base, 36-point, with shield ground lug and removable terminal blocks. IC695ALGxxx, IC69xMDL660 and IC694MDL664 modules only. Discrete output modules not supported.	Active
-------------	--	--------

HDTBQC Interface Cables

IC694CBL005	Shielded 0.5 meter cable with termination on both ends. IC694TBC032 and IC694RTB032 only.	Active
IC694CBL010	Shielded 1.0 meter cable with termination on both ends. IC694TBC032 and IC694RTB032 only.	Active
IC694CBL030	Shielded 3.0 meter cable with termination on both ends. IC694TBC032 and IC694RTB032 only.	Active
IC694CBL130	Shielded 3.0 meter cable with termination on one end that connects to the IC694TBC032 terminal block. The other end of the cable is non-terminated wires.	Active