

Terminal Blocks - P Series & Rail Accessories

P Series - Feed Through Terminal Blocks



PDU 2.5/4

Ratings/Width	Wire Range	Part Number	Description
600V/30/5mm	26-10 AWG	1896110000	PDU 2.5/4
600V/30/5mm	26-10 AWG	1896120000	PDU 2.5/4 3AN
600V/30/5mm	26-10 AWG	1896130000	PDU 2.5/4 4AN
600V/5mm	26-10 AWG	1896170000	PPE 2.5/4
600V/5mm	26-10 AWG	1896200000	PPE 2.5/4 3AN
600V/5mm	26-10 AWG	1896160000	PPE 2.5/4 4AN

P Series - Ground Terminal Blocks




PPE 2.5/4

Rail Accessories



TS35 7.5x1.0



TS35 15x1.5



TS35 15x2.3



TS32

Solid		M5 Slot		M6 Slot		End Bracket	
TS35x7.5	0383400000	TS35x7.5	0514500000	TS35x7.5	0676200000	EW35	0383560000
						WEW/2	1061200000
						WEW35/1	1059000000
						ZEW TS35	9540000000
						ZEW 35/2	8630740000
TS35x15	0236400000	TS35x15	0236500000			EW35	0383560000
						WEW/2	1061200000
						WEW35/1	1059000000
						ZEW TS35	9540000000
						ZEW 35/2	8630740000
TS35x15	0498000000					EW35	0383560000
						WEW/2	1061200000
						WEW35/1	1059000000
						ZEW TS35	9540000000
						ZEW 35/2	8630740000
TS32	0122800000	TS32	0514400000	TS32	0676100000	EWK1	0206160000
						EWK2	0199360000
						WEW32/1	1067600000
						EWK	0495160000


Terminal Blocks - P Series & Rail Accessories

End Plate / Partition	End Bracket *	Jumpers (# of poles)	Labels	DIN Rail *	Screwdriver
1896300000	9540000000	1908960000 (20)	1635000000	0514500000	9008320000
1896480000	9540000000	1908960000 (20)	1635000000	0514500000	9008320000
1896320000	9540000000	1908960000 (20)	1635000000	0514500000	9008320000
1896300000	9540000000	N/A	1635000000	0514500000	9008320000
1896480000	9540000000	N/A	1635000000	0514500000	9008320000
1896320000	9540000000	N/A	1635000000	0514500000	9008320000

Mounting Bases



Description	Part Number
FM 4 (M4) TS 35	0687900000
FM 5 (M5) TS35	0636800000
FM 6 (M6) TS35	0636900000



Description	Part Number
MOFU 35/LO/1	0646260000





Description	Part Number
MOFU 35	0495660000



Description	Part Number
MB M3/M5 TS32	0503500000
MB M5/M3 TS32	0553400000
MB M6/M4 TS32	0334900000

Rail Support - straight



Rail Support - straight

TST 2/M5	1286600000
TST 2/M6	0101700000
TST 30mm	7924270030
TST 40mm	7924270040
TST 50mm	7924270050
TST 70mm	7924270070
TST 90mm	7924270090

Rail Support - angled

TSTW 5/M5	01781035000
TSTW 5/M6	1779103500
TSTW 6/M6	0164003500
TSTW 49mm	7924273549
TSTW 58mm	7924273558
TSTW 68mm	7924273568
TSTW 78mm	7924273578
TSTW 88mm	7924273588
TSTW 98mm	7924273598

Rail Support - screws

FKSC M5X8	0295900000
FKSC M6X8	0642600000
FKSC M6X12	0353500000

SH 1 TS 15 compl.	0299860000
SH 1 socket	0401460000
SH 1 yoke	0635900000
SH 2 TS 32/35	0494920000
SH 2 S	0641720000

SchT5	0292460000
ESO 5 white	1607710000
STR5	0294000000
SchT5S	1631930000
ESO5S white	1631920000
STR5S	1631940000

* See page A.16 for details or other options