


Terminal Blocks - SAK Series

SAK Series - Feed Through Terminal Blocks



SAK 4/EN

Ratings/Width	Wire Range	Part Number	Description
600V/25A/6mm	26-10 AWG	0380420000	SAK 2.5/35 KRG
600V/25A/6mm	26-10 AWG	0279620000	SAK 2.5 KRG
600V/25A/6mm	26-10 AWG	0380460000	SAK 2.5/35 PA
600V/25A/6mm	26-10 AWG	0279660000	SAK 2.5 PA
600V/25A/6mm	26-10 AWG	0218660000	SAK 2.5/EN
600V/36A/6.5mm	26-10 AWG	0443620000	SAK 4/35 KRG
600V/36A/6.5mm	26-10 AWG	0128320000	SAK 4 KRG
600V/36A/6.5mm	26-10 AWG	0443660000	SAK 4/35 PA
600V/36A/6.5mm	26-10 AWG	1716240000	SAK 4 PA
600V/36A/6.5mm	26-10 AWG	0467460000	SAK 4/EN
600V/47A/8mm	20-8 AWG	0380520000	SAK 6N/35 KRG
600V/47A/8mm	20-8 AWG	0193220000	SAK 6N KRG
600V/47A/8mm	20-8 AWG	0380560000	SAK 6/35 PA
600V/47A/8mm	20-8 AWG	0193260000	SAK 6N PA
600V/47A/8mm	26-8 AWG	0212860000	SAK 6 EN
600V/65A/10mm	14-6 AWG	0443720000	SAK 10/35 KRG
600V/65A/10mm	14-6 AWG	0110020000	SAK 10 KRG
600V/65A/10mm	14-6 AWG	0443760000	SAK 10/35 PA
600V/65A/10mm	14-6 AWG	0110060000	SAK 10 PA
600V/65A/10mm	16-16 AWG	0337660000	SAK 10 EN
600V/87A/12mm	10-4 AWG	0380620000	SAK 16/35 KRG
600V/87A/12mm	10-4 AWG	0271020000	SAK 16 KRG
600V/87A/12mm	10-4 AWG	0380660000	SAK 16/35 PA
600V/87A/12mm	10-4 AWG	0271060000	SAK 16 PA
600V/87A/12mm	10-4 AWG	0339760000	SAK 16 EN
600V/145A/18mm	6-2 AWG	0608220000	SAK 35N/35 KRG
600V/145A/18mm	6-2 AWG	0303520000	SAK 35 KRG
600V/120A/18mm	12-2 AWG	0608260000	SAK 35N/35 PA
600V/120A/18mm	12-2 AWG	0550660000	SAK 35N PA
600V/145A/18mm	6-2 AWG	0339860000	SAK 35 EN