
# Wallplates and accessories | Designer | Claro and Satin Colors



### **Product family features**

- · Can be used in conjunction with the following dimmer(s) and switch(es): Maestro®, Maestro IR®, Maestro Wireless®, Pico® wireless control, Diva®, Skylark Contour®, Skylark<sub>®</sub>
- · All Lutron wallplates are screwless, seamless, and have no visible hardware; the front plate securely snaps into the alignment adapter plate
- Full line of wiring devices in Designer style opening
- · Blank inserts available for Gloss colors (DV-BI-) and Satin Colors® (SC-BI-)
- · Customize your designer wallplate with engraving. Contact customer service to get started; 1.888.LUTRON1

### Ganging and derating

- · Designer wallplates use standard ganging
- Requires fins to be removed from dimmers for proper spacing ("Fins Broken" ganging), see pg. 179
- May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables, pg. 179

#### **Available finishes**

Use **BOLD** color code in model number (Example: SC-1-PL)

Gloss finishes



<sup>\*</sup>Stainless Steel finish wallplates include black plastic trim/adapter, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.

# Wallplates and accessories | Designer | Claro<sub>®</sub> and Satin Colors<sub>®</sub>

## Wallplates for Maestro®, Maestro IR®, Maestro Wireless®, Pico® wireless control, Diva®, Skylark Contour® and Skylark®



1-gang\*

CW-1-XX<sup>1</sup> SC-1-XX<sup>2</sup>

W: 2.94 in (75 mm); H: 4.69 in (119 mm)


P: .30 in (7.6 mm)



4-gang\* CW-4-XX<sup>1</sup> SC-4-**XX**<sup>2</sup>

W: 8.37 in (213 mm); H: 4.69 in (119 mm);


P: .30 in (7.6 mm)



2-gang\* CW-2-**XX**<sup>1</sup> SC-2-**XX**<sup>2</sup>

W: 4.75 in (121 mm); H: 4.69 in (119 mm);


P: .30 in (7.6 mm)



5-gang\* CW-5-XX<sup>1</sup> SC-5-XX<sup>2</sup>

W: 10.18 in (259 mm); H: 4.69 in (119 mm);

P: .30 in (7.6 mm)



CW-3-**XX**<sup>1</sup> 3-gang\*  $SC-3-XX^2$ 

W: 6.56 in (167 mm); H: 4.69 in (119 mm);

P: .30 in (7.6 mm)

**XX**<sup>1</sup>: Gloss and Stainless Steel color codes, see pg. 170

XX<sup>2</sup>: Satin Colors<sub>®</sub> codes, see pg. 170

#### **Important notes**

 Multiple devices with line and low-voltage can be mounted behind a common wallplate using a standard barrier backbox. See Application Note #213 (Combining Low-Voltage and Line Voltage Wiring Devices in a Multi-Gang Box) at www.lutron.com/applicationnotes.

Multi-gang dimmer installations may require derating, see pg. 179.

\*Stainless Steel finish wallplates include black plastic trim/adapter, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.