



POWER MANAGEMENT

PRODUCT	PART #	DESCRIPTION
lyriQ™ High Performance Keypad Power Module 	AU1001	<p>The lyriQ High Performance Power Module supports up to four lyriQ High Performance Keypads. It's a single-slot module and features dual power input connections.</p> <p>Bracket included.</p>
PRODUCT	PART #	DESCRIPTION
Universal Power Distribution Module 	PW1010	<p>This Power Distribution Module distributes 5 VDC, 9 VDC, 12 VDC, 15 VDC and 24 VDC out of one 60 W power supply. It features three 24 VDC output connections, three 12 VDC output connections, and two independent, user-selectable DC voltage outputs.</p> <p>Bracket included. Includes 60 W Power Supply (PW1060) and six female power cables.</p>
PRODUCT	PART #	DESCRIPTION
24 VDC, 60 W Desk-Mount Power Supply 	PW1060	<p>Powers the lyriQ Audio Module, LCD Module, and Universal Power Distribution Module.</p>
PRODUCT	PART #	DESCRIPTION
24 VDC, 120 W Power Supply Kit 	PW1120	<p>This power kit includes two 24 V, 60 W power supplies as well as a stackable bracket to free up space and reduce clutter in the enclosure. It is ideal for supporting the lyriQ high performance system.</p> <p>Kit contains: 2 24 V, 60 W Power Supplies 1 Bracket 1 Custom Power Strip Velcro Straps</p>
PRODUCT	PART #	DESCRIPTION
24 VDC, 240 W Power Supply Kit 	PW1240	<p>With four power supplies and two stackable brackets, this new kit provides all the power needed in the enclosure without wasting space. The 24 V, 60 W power supplies can be plugged into the power strip and stacked within the brackets to enable an easier and more attractive installation. It is ideal for supporting the lyriQ high performance system.</p> <p>Kit contains: 4 24 V, 60 W Power Supplies 2 Brackets 1 Custom Power Strip Velcro Straps</p>




HIGH PERFORMANCE UNITY HOME SYSTEM

Amp up the Unity Home System with four rooms of high-performance audio, a full Selective Call Intercom System, four cameras, and two versatile viewing options.

HIGH PERFORMANCE UNITY / BILL OF MATERIALS

PRODUCT	PART #	QUANTITY	PAGE
Integration Module	HA6001	1	62
LCD Console w/ High-Performance IyriQ	HA5010--XX	1	64
24 VDC, 60 W Desk-Mount Power Supply	PW1060	4	39
TV Display Interface	HA5201-XX	1	123
Selective Call Room Unit	IC5000-XX	3	103
Selective Call Video Door Unit	IC5003-XX	2	102
IyriQ Four-Source, Eight-Zone Distribution Module	AU1002	1	71
IyriQ Flush-Mount Single Source Input	AU1004-WH	1	72
IyriQ Flush-Mount Triple Source Input	AU1011-WH	1	72
IyriQ High-Performance Keypad in Studio Design	AU5010-XX	3	73
IyriQ Local Source Input in Studio Design	AU5008-XX	2	72
IyriQ High-Performance Power Module	AU1001	1	39
Dual IR Mouse Emitter	F7425	2	73
Universal IR Target	AC1016	1	73
6.5" evoQ 5000 In-Ceiling Speaker	HT5650	8	87
6.5" In-Ceiling Pre-Construction Speaker Bracket	364672-02	4	89
Ball Camera	CM5002-XX	2	122
3-Gang Studio Wall Plate	WP5003-WH	3	32

HIGH PERFORMANCE UNITY / WIRING DIAGRAM






ULTIMATE UNITY HOME SYSTEM

Four sources of audio, four cameras and two viewing options give this system everything a homeowner needs to be connected in their home.

ULTIMATE UNITY / BILL OF MATERIALS

PRODUCT	PART #	QUANTITY	PAGE
Integration Module	HA6001	1	62
LCD Console w/ lyriQ	HA5009-XX	1	64
24 VDC, 60 W Desk-Mount Power Supply	PW1060	2	39
TV Display Interface	HA5201-XX	1	123
Selective Call Room Unit	IC5000-XX	3	103
Selective Call Video Door Unit	IC5003-XX	2	102
lyriQ Four-Source, Eight-Zone Distribution Module	AU1002	1	71
lyriQ Flush-Mount Single Source Input	AU1004-WH	1	72
lyriQ Flush-Mount Triple Source Input	AU1011-WH	1	72
lyriQ Keypad in Studio Design	AU5009-XX	3	73
lyriQ Local Source Input in Studio Design	AU5008-XX	2	72
Dual IR Mouse Emitter	F7425	2	73
Universal IR Target	AC1016	1	73
6.5" evoQ 3000 In-Ceiling Speaker	MS3650	4	88
6.5" In-Ceiling Pre-Construction Speaker Bracket	364672-02	4	89
Ball Camera	CM5002-XX	2	122
3-Gang Studio Wall Plate	WP5003-WH	3	32

ULTIMATE UNITY / WIRING DIAGRAM






PREMIUM UNITY HOME SYSTEM

Expand the Basic Unity Home System to include one source of music in four rooms.

PREMIUM UNITY / BILL OF MATERIALS

PRODUCT	PART #	QUANTITY	PAGE
Integration Module	HA6001	1	62
LCD Console w/ lyriQ	HA5009-XX	1	64
24 VDC, 60 W Desk-Mount Power Supply	PW1060	2	39
TV Display Interface	HA5201-XX	1	123
Selective Call Room Unit	IC5000-XX	3	103
Selective Call Video Door Unit	IC5003-XX	2	102
lyriQ Advanced Single Source Distribution Module	AU1014	1	71
lyriQ Flush-Mount Single Source Input	AU1004-WH	1	72
lyriQ Keypad in Studio Design	AU5009-XX	3	73
6.5" evoQ 3000 In-Ceiling Speaker	MS3650	4	88
6.5" In-Ceiling Pre-Construction Speaker Bracket	364672-02	4	89
Ball Camera	CM5002-XX	1	122
3-Gang Studio Wall Plate	WP5003-WH	3	32

PREMIUM UNITY / WIRING DIAGRAM






BASIC UNITY HOME SYSTEM

Help your homeowners experience truly integrated home systems with the Basic Unity Home System.

BASIC UNITY / BILL OF MATERIALS


PRODUCT	PART #	QUANTITY	PAGE
Integration Module	HA6001	1	62
LCD Console	HA5000-XX	1	64
24 VDC, 60 W Desk-Mount Power Supply	PW1060	1	39
TV Display Interface	HA5201-XX	1	123
Selective Call Room Unit	IC5000-XX	3	103
Selective Call Video Door Unit	IC5003-XX	1	102

BASIC UNITY / WIRING DIAGRAM



Crank up the volume with this high performance audio solution. This solution lets homeowners entertain throughout the house without missing a single riff of their favorite high fidelity audio.

PRODUCT	PART #	QUANTITY	PAGE
lyriQ High-Performance Keypad in Studio Design	AU5010-XX	4	73
lyriQ High-Performance Power Module	AU1001	1	39
lyriQ Flush-Mount Single Source Input	AU1004-XX	1	72
lyriQ Flush-Mount Triple Source Input	AU1011-XX	1	72
lyriQ Four-Source, Eight-Zone Distribution Module	AU1002	1	71
lyriQ Local Source Input in Studio Design	AU5008-XX	2	72
Home Systems Remote Control	AU1060	1	73
Dual IR Mouse Emitter	F7425	2	73
24 Volt, 2.5 Amp Power Supply	PW1060	3	39
evoQ 5000 6.5" In-Ceiling Speaker	HT5650	8	87
6.5" In-Ceiling Pre-Construction Speaker Bracket (2)	364672-02	4	89
Universal IR Target	F7426	1	73
1-Gang Studio Wall Plate	WP5001-XX	1	32
2-Gang Studio Wall Plate	WP5002-XX	1	32





PREMIUM MUSIC SOLUTION

Now the family doesn't have to share the same music over the whole house system. Homeowners can listen to any one of four audio sources in up to eight different locations at the same time.

PREMIUM MUSIC / BILL OF MATERIALS

PRODUCT	PART #	QUANTITY	PAGE
IyriQ Keypad in Studio Design	AU5009-XX	4	73
IyriQ Flush-Mount Single Source Input	AU1004-XX	1	72
IyriQ Flush-Mount Triple Source Input	AU1011-XX	1	72
IyriQ Four-Source, Eight-Zone Distribution Module	AU1002	1	71
IyriQ Local Source Input in Studio Design	AU5008-XX	1	72
Home Systems Remote Control	AU1060	1	73
Dual IR Mouse Emitter	F7425	2	73
24 Volt, 2.5 Amp Power Supply	PW1060	1	39
evoQ 3000 6.5" In-Ceiling Speakers (Pair)	MS3650	4	88
6.5" In-Ceiling Pre-Construction Speaker Bracket	364672-02	4	89
Universal IR Target	F7426	1	73
2-Gang Studio Wall Plate	WP5002-XX	1	32
1-Gang Studio Wall Plate	WP5001-XX	1	32

PREMIUM MUSIC / WIRING DIAGRAM

