

ENCLOSURES

PLASTIC

- Knockouts include screw driver holes for easy removal
- Includes four self-tapping screws for mounting and optional hardware to lock the cover
- Multiple compatible video, voice, and data distribution modules available
- Flush and surface-mount installation options



EN0802



EN0806

| PART NO. | DESCRIPTION |
|----------|--|
| EN0800 | 8-Inch MDU Enclosure And Cover |
| EN0801 | 8-Inch MDU Enclosure Cover |
| EN0802 | 8-Inch MDU Enclosure Kit (6 phone, 4 video) |
| EN0806 | 8-Inch MDU Enclosure Bulk Pack (6) |
| TM0106 | 6-Way Telephone Board (For use with EN0800) |
| TM0404 | Combo 4-Way Phone / 4 Port Cat 5e Data Board (For use with EN0800) |
| VM0104 | 4-Way Vertical 1Ghz Splitter (For use with EN0800) |
| VM0106 | 6-Way Vertical 1Ghz Splitter (For use with EN0800) |
| VM0108 | 8-Way Vertical 1Ghz Splitter (For use with EN0800) |
| VM0204 | 4-Way Vertical 2Ghz Splitter (For use with EN0800) |
| VM0206 | 6-Way Vertical 2Ghz Splitter (For use with EN0800) |
| VM0208 | 8-Way Vertical 2Ghz Splitter (For use with EN0800) |

DATA CONNECTIVITY

KEYSTONE INSERTS



WP346A-WH



WP3473-WH



WP3475-WH



WP3476-WH



WP3425-WH



WP3450-WH



WP3451-WH



WP3458-WH



WP3460-WH



WP3560-WH



WP3479-WH



WP3480-WH



WP3481-WH



WP3482-WH

QUICK CONNECT INSERTS

| PART NO. | DESCRIPTION |
|-----------|--|
| WP346A-XX | Cat 6a Quick Connect RJ45 Keystone Insert |
| WP3473-XX | RJ25 6-Position, 6-Conductor Telephone Keystone Insert |
| | 10 COUNT BULK PACKS IN WH AND LA (WP3473-XX-10) |
| WP3475-XX | Cat 5e Quick Connect RJ45 Keystone Connector |
| | 10 COUNT BULK PACKS IN WH AND LA (WP3475-XX-10) |
| | 50 COUNT BULK PACKS IN WH, LA AND BE (WP3475-XX-50) |
| | 100 COUNT BULK PACKS IN WH (WP3475-WH-100) |
| WP3476-XX | Cat 6 Quick Connect RJ45 Keystone Connector |
| | 10 COUNT BULK PACKS IN WH, LA AND BE (WP3476-XX-10) |
| | 25 COUNT BULK PACKS IN WH (WP3476-WH-25) |

COLORS:

BE, BK, BR, GY, GN, IV, LA, OR, RE, WH, YE

NOTES:

YOU CAN EASILY TERMINATE ALL WIRES AT ONCE USING THE AC3400 PUNCH & GO TOOL.

OTHER INSERTS

| PART NO. | DESCRIPTION |
|-----------|--|
| WP3425-XX | RJ25 6P6C Keystone Connector |
| | Colors: BK, BR, IV, LA, WH |
| WP3450-XX | Cat 5e RJ45 Keystone Connector |
| | Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH |
| WP3451-XX | Cat 5e RJ45 Keystone Coupler |
| | Colors: BK, WH |
| WP3458-XX | Cat 5e Keyed RJ45 Keystone Connector |
| | Colors: BK, BR, IV, LA, WH |
| WP3460-XX | Cat 6 RJ45 Keystone Connector |
| | Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH |
| WP3560-XX | Snap & Go Cat 6 Keystone Connector |
| | Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH |

COAX VIDEO INSERTS

| PART NO. | DESCRIPTION |
|-----------|--|
| WP3479-XX | Non-Recessed Coax Keystone F-Connector (1 GHz) |
| | 50 COUNT BULK PACK IN WH OR LA (WP3479-XX-50) |
| WP3480-XX | Recessed Gold F-Connector (3 GHz) |
| WP3481-XX | Recessed Nickle F-Connector (3 GHz) |
| | 50 COUNT BULK PACK IN WH (WP3481-WH-50) |
| WP3482-XX | Recessed Self-Terminating Keystone F-Connector (1 GHz) |

COLORS:

BK, BR, IV, LA, WH



DATA CONNECTIVITY

KEYSTONE INSERTS (CONT.)



AUDIO/VIDEO INSERTS

| PART NO. | DESCRIPTION |
|-----------|------------------------------------|
| WP3461-XX | White Keystone RCA-to-F Connector |
| WP3462-XX | Red Keystone RCA-to-F Connector |
| WP3463-XX | Green Keystone RCA-to-F Connector |
| WP3464-XX | Blue Keystone RCA-to-F Connector |
| WP3465-XX | Yellow Keystone RCA-to-F Connector |
| WP3466-XX | Purple Keystone RCA-to-F Connector |

Colors: BK, BR, IV, LA, WH

| | |
|-----------|------------------------------------|
| WP1234-XX | HDMI Keystone Coupler |
| WP3455-XX | Blank Keystone Insert |
| WP1215-XX | 3.5MM Stereo Coupler |
| WP3457-XX | Audio Keystone Binding Post (Pair) |
| WP3456-XX | Speaker Keystone Binding Post |

Colors: BK, BR, LA, WH

| | |
|----------|--|
| KSRCAYW | Keystone RCA-to-RCA (Yellow Insulator) |
| KSRCARW | Keystone RCA-to-RCA (Red Insulator) |
| KSRCABW | Keystone RCA-to-RCA (Black Insulator) |
| KSRCABEW | Keystone RCA-to-RCA (Blue Insulator) |
| KSRCAGNW | Keystone RCA-to-RCA (Green Insulator) |

USB & FIBER INSERTS

| PART NO. | DESCRIPTION |
|-----------|---------------------|
| WP1220-XX | USB 2.0 A/A Coupler |
| WP1221-XX | USB 2.0 A/B Adapter |
| WP1210-XX | MTRJ Coupler MM |
| WP1211-XX | LC Coupler MM |
| KSSCXX | SC Coupler MM |
| KSSTXX | ST Coupler MM |

COLORS: BK, BR, LA, WH



COLOR KEY:



NOTE: The following suffixes should be added to the end of all applicable part numbers. Omit color code to order brown device.

DATA CONNECTIVITY

KEYSTONE WALL PLATES



WALL PLATES


| PART NO. | DESCRIPTION |
|-------------|---|
| WP3401-XX | 1-Gang, 1-Port Wall Plate 10 COUNT BULK PACK IN WH OR LA (WP3401-XX-10) 25 COUNT BULK PACK IN WH OR LA (WP3401-XX-25) |
| WP3402-XX | 1-Gang, 2-Port Wall Plate 10 COUNT BULK PACK IN WH OR LA (WP3402-XX-10) 25 COUNT BULK PACK IN WH OR LA (WP3402-XX-25) |
| WP3403-XX | 1-Gang, 3-Port Wall Plate |
| WP3404-XX | 1-Gang, 4-Port Wall Plate |
| WP3406-XX | 1-Gang, 6-Port Wall Plate |
| COLORS: | BK, BR, IV, LA, WH, GY, SS |
| WP3212-XX | 2-Gang, 12-Port Wall Plate Colors: IV, LA, WH |
| DIMENSIONS: | 1-GANG: 2.9375" x 4.6875" 2-GANG: 8.375" x 4.6875" |

OVERSIZED WALL PLATES



| PART NO. | DESCRIPTION |
|-------------|--|
| WP3300-XX | 1-Gang, Blank Oversized Wall Plate |
| WP3301-XX | 1-Gang, 1-Port Oversized Wall Plate 10 COUNT BULK PACK IN WH OR LA (WP3301-XX-10) |
| WP3302-XX | 1-Gang, 2-Port Oversized Wall Plate 10 COUNT BULK PACK IN WH OR LA (WP3302-XX-10) |
| WP3303-XX | 1-Gang, 3-Port Oversized Wall Plate |
| WP3304-XX | 1-Gang, 4-Port Oversized Wall Plate |
| WP3306-XX | 1-Gang, 6-Port Oversized Wall Plate |
| COLORS: | WH, LA |
| DIMENSIONS: | 1-GANG: 3.3125" x 5.0625" |

LABELED WALL PLATES



| PART NO. | DESCRIPTION |
|-------------|------------------------------------|
| KTPDL1XX | 1-Port Keystone Labeled Wall Plate |
| KTPDL2XX | 2-Port Keystone Labeled Wall Plate |
| KTPDL3XX | 3-Port Keystone Labeled Wall Plate |
| KTPDL4XX | 4-Port Keystone Labeled Wall Plate |
| KTPDL6XX | 6-Port Keystone Labeled Wall Plate |
| COLORS: | I, LA, W |
| DIMENSIONS: | 1-GANG: 2.9375" x 4.6875" |

DATA CONNECTIVITY

KEYSTONE WALL PLATES



TP13W



TP26W




TP262W



TP263W



TP264W



TPJ13W



TPJ26W



TPJ262W



TPJ263W



TPJ264W

STANDARD DECORATOR WALL PLATES

| PART NO. | DESCRIPTION |
|----------|-----------------------------|
| TP13XXX | 1-Gang Blank Wall Plate |
| TP26XXX | 1-Gang Decorator Wall Plate |
| TP262XXX | 2-Gang Decorator Wall Plate |
| TP263XXX | 3-Gang Decorator Wall Plate |
| TP264XXX | 4-Gang Decorator Wall Plate |

| | |
|-------------|--|
| COLORS: | BK, I, LA, W, GRY (for Brown, leave blank) |
| DIMENSIONS: | 1-GANG: 2.9375" x 4.6875" 2-GANG: 4.75" x 4.6875" |
| | 3-GANG: 6.563" x 4.6875" 4-GANG: 8.375" x 4.6875" |

JUMBO DECORATOR WALL PLATES

| PART NO. | DESCRIPTION |
|-----------|-------------------------------|
| TPJ13XXX | Jumbo 1-Gang Blank Wall Plate |
| TPJ26XXX | Jumbo 1-Gang Wall Plate |
| TPJ262XXX | Jumbo 2-Gang Wall Plate |
| TPJ263XXX | Jumbo 3-Gang Wall Plate |
| TPJ264XXX | Jumbo 4-Gang Wall Plate |

| | |
|-------------|---|
| COLORS: | BK, I, LA, W, GRY (for Brown, leave blank) |
| DIMENSIONS: | 1-GANG: 3.3125" x 5.0625" 2-GANG: 5.125" x 5.0625" |
| | 3-GANG: 6.9375" x 5.0625" 4-GANG: 8.75" x 5.0625" |

KEYSTONE DECORATOR STRAPS



WP3410-WH



WP3411-WH



WP3412-WH



WP3413-WH



WP3414-WH



WP3416-WH

| PART NO. | DESCRIPTION |
|-----------|--|
| WP3410-XX | Blank Decorator Outlet Strap |
| WP3411-XX | 1-Port Decorator Outlet Strap |
| | 10 COUNT BULK PACK IN WH OR LA (WP3411-XX-10) |
| WP3412-XX | 2-Port Decorator Outlet Strap |
| WP3413-XX | 3-Port Decorator Outlet Strap |
| | 10 COUNT BULK PACK IN WH OR LA (WP3413-XX-10) |
| WP3414-XX | 4-Port Decorator Outlet Strap |
| WP3416-XX | 6-Port Decorator Outlet Strap |

| | |
|---------|------------------------|
| COLORS: | BK, BR, IV, LA, WH, GY |
|---------|------------------------|

COLOR KEY:



NOTE: The following suffixes should be added to the end of all applicable part numbers. Omit color code to order brown device.

DATA CONNECTIVITY

SURFACE MOUNT BOXES



WP3409-WH



WP3501-WH



WP3502-WH



WP3504-WH



WP3506-WH

| PART NO. | DESCRIPTION |
|-----------|-------------------------------|
| WP3409-WH | Single Gang Surface Mount Box |
| WP3501-WH | Surface Mount Box 1-Port |
| WP3502-WH | Surface Mount Box 2-Port |
| WP3504-WH | Surface Mount Box 4-Port |
| WP3506-WH | Surface Mount Box 6-Port |

COLORS: IV, LA, WH

PRE-MOLDED WALL PLATES & STRAPS



TPE1W



TPE2W



WMTE14W



SMTE14I



TPCATW



TPCATV2W



TPELTVW



26TELTW



WP2002-WH



WP3467-WH



WP9001-WH



WP9002-WH

| PART NO. | DESCRIPTION |
|-----------|---|
| TPE1XX | 2-Line Telephone Jack Wall Plate (4 Conductor Configuration) Colors: BK, BR, I, LA, W, GRY |
| TPE2XX | Dual 2-Line Telephone Jack Wall Plate (4 Conductor Configuration) Colors: BK, BR, I, LA, W |
| WMTE14W | Modular Wall Mount Telephone Jack for Hanging Phones Colors: W |
| SMTE14I | Surface Mount Modular 2-Line Telephone Jack (4 Conductor Configuration) Colors: I |
| TPCATVXX | 1 GHz Coaxial Connector & Wall Plate Colors: I, LA, W, BR, BK |
| TPCATV2XX | Dual 1 GHz Coaxial Connector Wall Plate Colors: I, LA, W, BR, BK |
| TPELTVXX | 1 GHz Coaxial Connector & 2-Line Phone Jack Wall Plate Colors: I, LA, W, BR, BK |
| 26TELTVXX | 1 GHz Coaxial Connector & 2-Line Phone Jack with 1-Piece Molded Decorator Plate Colors: I, LA, W |
| WP2002-WH | 1-Gang 6P6C RJ25 Terminating Wall Phone Plate Colors: WH |
| WP3467-XX | Keystone Wall Phone Plate Colors: WH, SS (Stainless Steel) |
| WP9001-XX | Single Gang Bullnose Wall Plate Colors: BK, WH |
| WP9002-XX | Double Gang Bullnose Wall Plate Colors: BK, WH |

