


# KEYSTONE JACKS & MODULES

TechChoice keystone jacks and modules feature an easy-to-follow universal wiring label and support standard termination using a 110-impact tool. The keystone footprint allows for the greatest flexibility in installation scheduling because its rear insertion into the faceplate allows the technician to complete the termination before, during and after the construction process.

## Keystone Jacks



PART NO. Single Pack	PART NO. Pack of 25	DESCRIPTION
OR-KS6A	OR-KS6	Category 6, 8-position, T568A/B wiring, icon compatible.
OR-KS5EA	OR-KS5E	Category 5e, 8-position, T568A/B wiring, icon compatible.
OR-KSRJ25A	OR-KSRJ25	RJ25, 6 position jack, USOC wiring, icon compatible
	OR-KSICON	TechChoice keystone icon, 2 sided voice/data, package of 25

Add tailcode to end of part number (example: OR-KS6-42).  
WM indicates Wiremold color match.

fog white	-00	-13	-36	-42	-88	-99	-43	-44	-45	-78
	WM				WM	WM				WM

RJ25 Color Choices     
 Category 5e and 6 Color Choices

-00=Black; -13=Electrical ivory; -36=Blue; -42=Red; -88=White;  
 -99=Wiremold® ivory; -43=Orange; -44=Yellow, -45=Green; -78=Gray.  
 Standard color is fog white, requiring no tail code.

## Fiber Keystone Modules




PART NO.	DESCRIPTION
OR-KSST	1-ST simplex multimode, phosphor-bronze alignment sleeves, 180° exit. Fog white. Sold with dust cover
OR-KSSC	1-SC simplex multimode, phosphor-bronze alignment sleeves, 180° exit. Fog white. Sold with dust cover
OR-KSLC	1-LC (2 fibers) multimode, phosphor-bronze alignment sleeves, 180° exit. Fog white. Sold with dust cover
OR-KSMTRJ	1 MT-RJ (2 fibers) multimode, feed-through, 180° exit, flush. Fog white. Sold with dust cover

NOTE: For Wiremold Ivory, add tail code of -99 to end of part number (example OR-KSST-99) Sold individually.

# KEYSTONE JACKS & MODULES

## Multimedia Keystone Modules



PART NO.	DESCRIPTION
OR-KSHDMI	HDMI, female to female, 19pin
OR-KSSV	S-Video to 110
OR-KSSVIDC	S-Video, female to female
OR-KSRCAR	RCA red to 110
OR-KSRCAG	RCA green to 110
OR-KSRCABL	RCA blue to 110
OR-KSRCAY	RCA yellow to 110
OR-KSRCAW	RCA white to 110
OR-KSRCAB	RCA black to 110
OR-KS35ST	3.5mm, stereo jack, female to female
OR-KS35STST	3.5mm, stereo jack, female to screw term
OR-KS14ST	1/4" stereo jack, female to solder
OR-KSUBAA	USB 2.0 A-A, female to female
OR-KSUBAB	USB 2.0 A-B, female to female
OR-KSBP	Binding post, set of 2
OR-KSBNC75	BNC 75 ohm, female to female, 75 ohm
OR-KSBNC	BNC 50 ohm, female to female, 50 ohm
OR-KSFCN	F Conn 75 ohm, female to female
OR-KSFCNR	F Conn 75 ohm, recessed, female to female
OR-KSS2210	Series II bezel, 2port, TechChoice keystone, 1 unit, 10pk
OR-KSB10	Blank, package of ten

NOTE: Standard color is fog white.  
For other colors, contact sales.