

# FACEPLATES

OR-KSFP4V110



## VGA Faceplates

VGA Faceplates are available in high impact 94V-0 rated thermoplastic. The single gang version includes one integrated VGA connector. The double gang version includes two VGA connectors.

PART NO.	DESCRIPTION
OR-KSFP4V110	Single-gang, holds four keystones, VGA to 110
OR-KSFP4VFT	Single-gang, holds four keystones, VGA with crimp pins
OR-KSFP8V110	Double-gang, holds eight keystones, two VGA to 110
OR-KSFP8VFT	Double-gang, holds eight keystones, two VGA with crimp pins

NOTE: Standard color is fog white. Add -13 for electrical ivory.

OR-KSFP2



## Faceplates

TechChoice® faceplates are available in high impact 94V-0 rated thermoplastic and stainless steel, with a variety of port capacities to match your workstation applications. All faceplates allow for a flush jack finish.

## Plastic Faceplates with Label Fields

PART NO.	DESCRIPTION
OR-KSFP1	Single gang, holds one keystone
OR-KSFP2	Single gang, holds two keystones
OR-KSFP3	Single gang, holds three keystones
OR-KSFP4	Single gang, holds four keystones
OR-KSFP6	Single gang, holds six keystones
OR-KSFP8	Dual gang, holds eight keystones
OR-KSFP12	Dual gang, holds 12 keystones

NOTE: Standard color is fog white. Add -13 for electrical ivory, -88 for white or -99 for Wiremold ivory.

OR-KSSS3



## Stainless Steel Faceplates with Label Fields

PART NO.	DESCRIPTION
OR-KSSS1	Single gang, holds one keystone
OR-KSSS2	Single gang, holds two keystones
OR-KSSS3	Single gang, holds three keystones
OR-KSSS4	Single gang, holds four keystones
OR-KSSS6	Single gang, holds six keystones
OR-KSSS8	Dual gang, holds eight keystones
OR-KSSS12	Dual gang, holds 12 keystones

OR-KSFPR2



## Plastic Faceplates without Label Fields

PART NO.	DESCRIPTION
OR-KSFPR1	Single gang with one keystone opening
OR-KSFPR2	Single gang with two keystone openings
OR-KSFPR3	Single gang with three keystone openings
OR-KSFPR4	Single gang with four keystone openings
OR-KSFPR6	Single gang with six keystone openings

NOTE: Standard color is fog white. Add -13 for electrical ivory, -88 for white or -99 for Wiremold ivory.

OR-KSD4



## Plastic Rectangular GFCI & 106 Frames

PART NO.	DESCRIPTION
OR-KSDS2	Stylistic rectangular frame with 2 keystone openings
OR-KSDS3	Stylistic rectangular frame with 3 keystone openings
OR-KSDS4	Stylistic rectangular frame with 4 keystone openings
OR-KS106S2	106 style frame with 2 keystone openings
OR-KS106S4	106 style frame with 4 keystone openings

NOTE: Standard color is fog white. Add -13 for electrical ivory, -88 for white or -99 for Wiremold ivory.

OR-KS106S4

