

Tamper-Resistant 15A Nightlight/GFCI, White

1595NTLTRWCC4



From the innovator of the product category, comes a full range of Pass & Seymour®GFCI receptacles to enhance safety, shorten installation times and increase productivity on the jobsite. Our tamper-resistant nightlight/GFCI ensure safety and convenience. LED illumination has a 20+ year life expectancy, which means no bulbs to change.

features & benefits

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Sealed nightlight with high impact-resistant Lexan® lens prevents tampering.
- Nightlight uses cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.
- LED Rated at 186 milliwatts 120V.
- Two receptacles.
- Photocell turns nightlight ON in dark, OFF in daylight.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10-#14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 10kA short circuit wiring.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.

- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: White

Available Colors: White, ivory, light almond, black, antique brass, dark bronze, nickel, titanium

Type: Nightlight/GFCI

Special Features: Tamper Resistant

Style: Decorator

Listing Agencies/Third Party Information

cULus: Yes

Federal Spec: Yes

Fed Spec Number: WC596

UL Listing No: UL498

UL Standard: Yes

UN SPS C: 39121704

Dimensions

Depth U S: 1.13"

Height U S: 4.2"

Width U S: 1.72"

Technical Information

Amps: 15A

NEMA Configuration Number: 5-15R

NEMA Rating: Yes

Volts: 125V

Volts A C: 125

Buy American Act Compliance

Country of Origin: CHINA

Buy American Act Status: No