



Straight Blade Receptacles TradeMaster® Decorator Hallway Lights & Combination Devices


Pass & Seymour




TMHWLCC



TMHWLECC



TM8HWLWCC



TM8HWLEWCC4

Straight Blade Receptacles

Hallway Lights & Combination Devices

Features	
<ul style="list-style-type: none"> Impact-resistant face and body. GE Lexan™ high impact-resistant lens. External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG. Ground screw position under the end of the strap minimizes the risk of contact. 	<ul style="list-style-type: none"> Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement. Sensor automatically turns light ON in the dark. Increased light output for better illumination. Light sensor for enhanced sensitivity.

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	3rd Party Compliance
				cUL _{us} UL1598
TradeMaster® Decorator Full Hallway Light				
TMHWLCC	— 120	0.1328	Clear	•
Enhanced Decorator Full Hallway Light with Light Sensor				
TMHWLECC	— 120	1.079	Clear	•
Enhanced Decorator Full Hallway Light without Light Sensor				
TMHWLENSCC	— 120	1.113	Clear	•
Full Hallway Decorator Light for use with P&S Metal Louver Plates**				
TMHWLLOUVCC	— 120	0.0843	Clear	•

*FCD = Foot Candle Distance. 1 Lumen = 1 FCD. See Page U-55 for more information.

**For Louver Plates, see Page S-20.

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance
					cUL _{us} UL498
TradeMaster® Decorator Hallway Light & Single Receptacle					
TM8HWLICCC	15 120/125	0.1442	Ivory	5-15R	•
TM8HWLWCC	15 120/125	0.1442	White	5-15R	•
TM8HWLBKCC	15 120/125	0.1442	Black	5-15R	•
TM8HWLCC	15 120/125	0.1442	Brown	5-15R	•
TM8HWLLACC	15 120/125	0.1442	Light Almond	5-15R	•
Enhanced Decorator Hallway Light & Single Receptacle					
TM8HWLEICC	15 120/125	0.2561	Ivory	5-15R	•
TM8HWLEWCC	15 120/125	0.2561	White	5-15R	•
TM8HWLELACC	15 120/125	0.2561	Light Almond	5-15R	•

*FCD = Foot Candle Distance. 1 Lumen = 1 FCD. See Page U-55 for more information.

2 Pole, 3 Wire



NEMA 5-15R

For complete line of Decorator Combination Devices and Hallway Lights, see Pages E-7 – E-11, E-17, E-18, E-21, E-30, E-36 and E-72.

All devices listed on this page conform to NEMA WD-1 and WD-6.