

Reflective Memory Interface Modules for PCs

PMC 5565 Reflective Memory PMC Module

PMC-5565PIORC-110000	PMC, 2 GIGA Baud RM w/FO Options, 128 Mbyte Memory, 4K FIFOs, Multimode Transmission	Active
PMC-5565PIORC-111000	PMC, 2 GIGA Baud RM w/FO Options, 128 Mbyte Memory, 4 K FIFOs, Single Mode Transmission	Active
PMC-5565PIORC-210000	PMC, 2 GIGA Baud RM w/FO Options, 256 Mbyte Memory, 4K FIFOs, Multimode Transmission	Active
PMC-5565PIORC-211000	PMC, 2 GIGA Baud RM w/FO Options, 256 Mbyte Memory, 4 K FIFOs, Single Mode Transmission	Active

PCI 5565 Reflective Memory PCI Module

PCI-5565PIORC-110000	PCI, 2 GIGA Baud RM w/FO Options, 128 Mbyte Memory, 4K FIFOs, Multimode Transmission	Active
PCI-5565PIORC-111000	PCI, 2 GIGA Baud RM w/FO Options, 128 Mbyte Memory, 4K FIFOs, Single Mode Transmission	Active
PCI-5565PIORC-210000	PCI, 2 GIGA Baud RM w/FO Options, 256 Mbyte Memory, 4K FIFOs, Multimode Transmission	Active
PCI-5565PIORC-211000	PCI, 2 GIGA Baud RM w/FO Options, 256 Mbyte Memory, 4K FIFOs, Single Mode Transmission	Active

PCI Express 5565 Reflective Memory PCIE Module

PCIE-5565RC-100000	PCI Express, 2 GIGA Baud RM w/FO Options, 128 Mbyte Memory, 4K FIFOs, Multimode Transmission	Active
PCIE-5565RC-101000	PCI Express, 2 GIGA Baud RM w/FO Options, 128 Mbyte Memory, 4K FIFOs, Single Mode Transmission	Active
PCIE-5565RC-200000	PCI Express, 2 GIGA Baud RM w/FO Options, 256 Mbyte Memory, 4K FIFOs, Multimode Transmission	Active
PCIE-5565RC-201000	PCI Express, 2 GIGA Baud RM w/FO Options, 256 Mbyte Memory, 4K FIFOs, Single Mode Transmission	Active

CMX and RMX Reflective Memory HUB (Contact GE for additional HUB configurations)

HUB-5595-308	DIN-rail Mount Reflective Memory Hub. 21 -32 VDC Power supply, 1x 10BaseT Ethernet, 1x RS232, 8x Multimode Pluggable transceivers	Active
HUB-5595-380	DIN-rail Mount Reflective Memory Hub. 21 -32 VDC Power supply, 1x 10BaseT Ethernet, 1x RS232, 8x Single mode Pluggable transceivers	Active
ACC-5595-208	Rack Mount or Desktop Reflective Memory Hub. Universal power supply, 1x 10BaseT Ethernet, 1x RS232, 8x multimode pluggable transceivers	Active
ACC-5595-280	Rack Mount or Desktop, 8 Single mode Pluggable Transceivers. And no Multimode Pluggable Transceivers	Active

Starter Kits (Only one starter kit per customer per customer site)

IC695STK001	RX3i Controller PACKage 1 Starter Kit includes RX3i with software. (includes one each IC695CPU305, IC695CHS012, IC695LRE001, IC695PSA040, IC695ETM001, IC694ACC300, IC694MDL940 and IC646MPP001.) Limited one RX3i starter kit per customer site.	Active
IC695STK002	RX3i with Control and View. Power PACKage 2 Starter Kit includes RX3i and QuickPanel View 6" STD with software. (includes one each IC695CPU305, IC695CHS012, IC695LRE001, IC695PSA040, IC695ETM001, IC694ACC300, IC694MDL940, IC754VSI06STD, BC646MQP001, IC646MPP001 and DC power supply for QuickPanel) Limited one RX3i starter kit per customer site.	Active
IC695STK003	RX3i, The Complete PACKage with Control, Motion and View. Power PACKage 3 Starter Kit includes RX3i, motion module (Servo and Amplifier sold separately) and QuickPanel View 6" STD with software. (includes one each IC695CPU305, IC695CHS012, IC695LRE001, IC695PSA040, IC695ETM001, IC694DSM314, IC694ACC300, IC694MDL940, IC754VSI06STD, BC646MQP001, IC646MPP001 and DC power supply for QuickPanel) Limited one RX3i starter kit per customer site.	Active
IC695STK004	RX3i Power PACKage 4 Starter Kit includes (one each IC695CPU305, IC695CHS012, IC695PSA040, IC695ETM001, IC646MPP101)	Active
IC695STK005	RX3i Power PACKage 5 Starter Kit includes (one each IC695CPU305, IC695CHS012, IC695PSA040, IC646MPP101)	Active
IC695STK006	RX3i Power PACKage 6 Starter Kit includes (one each IC695CPU305, IC695CHS012, IC695PSD040, IC695ETM001, IC646MPP101)	Active
IC695STK007	RX3i Power PACKage 7 Starter Kit includes (one each IC695CPU305, IC695CHS012, IC695PSD040, IC646MPP101)	Active
IC695STK010	RX3i CPE 305, RX3i PROFINET Controller Module, RX3i 7-slot base, RX3i AC Power Supply, RX3i 8 Point Input Simulator, RX3i 16 Point DC Outlet Module, VersaMax PROFINET Slave Module, VersaMax AC Power Supply, Mixed Discrete Module, Input Simulator, I/O Base, Proficy* Machine Edition Professional Software	Active