



LEED®



## Pass & Seymour



### Pass & Seymour® Vacancy Sensors/Occupancy Sensors/Timers

Make energy savings automatic!

- Simple installation and operation
- Easy time-delay selection
- More time-to-off choices
- Ergonomic switch for auto/manual off
- Integrated light level sensor with adjustable sensitivity
- Title 24 compliant
- Can contribute towards credits required to achieve LEED® certification



WESCO Part No.	Mfr.'s Model No.	Description
<b>TradeMaster® Vacancy Sensor Switches</b>		
785007-42224	CWP100I	Ivory
785007-42225	CWP100LA	Light Almond
785007-42226	CWP100W	White
<b>Wall Vacancy Sensors — No Neutral, 500W</b>		
785007-70500	RW500BBKCC4	Black
785007-70499	RW500BICC4	Ivory
785007-70514	RW500BLACC4	Light Almond
785007-70503	RW500BWCC4	White
<b>Wall Vacancy Sensors — with Neutral, 600W</b>		
785007-70502	RWU600BBKCC4	Black
785007-70512	RWU600BICC4	Ivory
785007-70515	RWU600BLACC4	Light Almond
785007-70505	RWU600BWCC4	White
<b>Wall Occupancy Sensors — No Neutral, 500W</b>		
785007-70508	RW500UBKCC4	Black
785007-70498	RW500UICC4	Ivory
785007-70507	RW500ULACC4	Light Almond
785007-70504	RW500UWCC4	White
<b>Wall Occupancy Sensors — with Neutral, 600W</b>		
785007-70510	RWU600UBKCC4	Black
785007-70511	RWU600UICC4	Ivory
785007-70496	RWU600ULACC4	Light Almond
785007-70506	RWU600UWCC4	White
<b>Wall Vacancy/Occupancy Sensors — 3-Way, with Neutral, 600W</b>		
785007-70564	RW3U600BK	Black
785007-70509	RW3U600BKCC4	Black
785007-70566	RW3U600I	Ivory
785007-70513	RW3U600IICC4	Ivory
785007-70563	RW3U600LA	Light Almond
785007-70497	RW3U600LACC4	Light Almond
785007-70565	RW3U600W	White
785007-70501	RW3U600WCC4	White
<b>Wall-Mount Occupancy Sensors — No Neutral</b>		
785007-23624	WSP200GRY	Gray
785007-23621	WSP200I	Ivory
785007-23623	WSP200LA	Light Almond
785007-23622	WSP200W	White
<b>PIR Occupancy Switch Sensors — Self Adaptive</b>		
785007-70383	OS300SGRY	Gray
785007-70386	OS300SI	Ivory
785007-70387	OS300SLA	Light Almond
785007-70379	OS300SW	White
<b>PIR Dual Relay Occupancy Switch Sensors — Self Adaptive</b>		
785007-70377	OSR300SGRY	Gray
785007-70378	OSR300SI	Ivory
785007-70381	OSR300SLA	Light Almond
785007-70374	OSR300SW	White

WESCO Part No.	Mfr.'s Model No.	Description
<b>PIR Ceiling Sensors</b>		
785007-70376	CS500	500SF
785007-70384	CS1200	1,200SF
<b>PIR Hallway Sensor</b>		
785007-60752	HS100I	90 Linear Ft.
<b>PIR Wide-Angle Sensor</b>		
785007-60758	WA100I	1200SF
<b>Dual-Tech Ceiling Sensor</b>		
785007-70523	CSD1000	1,000SF
<b>Ultrasonic Ceiling Sensors</b>		
785007-70388	CSU600	600SF
785007-70375	CSU1100	1,100SF
785007-70382	CSU2200	2,200SF
<b>Add-A-Relay</b>		
785007-60750	AR120/277	120V or 277V
<b>Power Packs</b>		
785007-70385	PWP2120	120V, 24VDC, 150MA
785007-70373	PWP2277	277V, 24VDC, 150MA
<b>Timers</b>		
785007-97015	97015I	15 Min., 1HP, 20A, 125V/10A, 250-277V, Ivory
785007-97020	97015LA	15 Min., 1HP, 20A, 125V/10A, 250-277V, Light Almond
785007-97018	97015W	15 Min., 1HP, 20A, 125V/10A, 250-277V, White
785007-97030	97030I	30 Min., 1HP, 20A, 125V/10A, 250-277V, Ivory
785007-97021	97030LA	30 Min., 1HP, 20A, 125V/10A, 250-277V, Light Almond
785007-97033	97030W	30 Min., 1HP, 20A, 125V/10A, 250-277V, White
785007-97060	97060I	60 Min., 1HP, 20A, 125V/10A, 250-277V, Ivory
785007-97063	97060W	60 Min., 1HP, 20A, 125V/10A, 250-277V, White
785007-97115	97115I	15 Min., 1HP, 20A, 125V/10A, 250-277V, Ivory
785007-97118	97115W	15 Min., 1HP, 20A, 125V/10A, 250-277V, White
785007-97130	97130I	30 Min., 1HP, 20A, 125V/10A, 250-277V, Ivory
785007-97133	97130W	30 Min., 1HP, 20A, 125V/10A, 250-277V, White
785007-97160	97160I	60 Min., 1HP, 20A, 125V/10A, 250-277V, Ivory
785007-97163	97160W	60 Min., 1HP, 20A, 125V/10A, 250-277V, White
785007-97352	97352I	1-60 Min. (DPDT), Center Off, 500W/3P, Ivory
785007-97355	97352W	1-60 Min. (DPDT), Center Off, 500W/3H, White
<b>Countdown Timers — 600W, 1/6HP</b>		
785007-23874	RT12BK	5 Min. to 12 Hrs., Black
785007-23876	RT12I	5 Min. to 12 Hrs., Ivory
785007-23875	RT12LA	5 Min. to 12 Hrs., Light Almond
785007-23878	RT12W	5 Min. to 12 Hrs., White
<b>7-Button Timers — 120 VAC, 1/6HP</b>		
785007-23877	RT1BK	1-60 Min., Black
785007-70390	RT1BKCC4	1-60 Min., Black
785007-23879	RT1I	1-60 Min., Ivory
785007-23872	RT1LA	1-60 Min., Light Almond
785007-23873	RT1W	1-60 Min., White



Energy Systems & Controls

