



LyriQ™ Multi-Room Audio System in the Classic Design



Attractive flush mount input simplifies installation and reduces clutter.

Whole house control is available via universal remote at the touch of a button.



Installation based on Cat 5 wiring is easy and efficient.

Classic design blends with any décor and complements Broadcast Intercom System in Classic Design.

AU1012-XX
LyriQ Single Source, 4-Zone Kit with Flush-Mount Input in Classic Design

INNOVATIVE TECHNOLOGY

WHOLE HOUSE CONTROL

Available from any keypad or from the universal remote, whole house control enables volume adjustment and source selection for the whole house system.

EASY EXPANSION

With the addition of the LyriQ Zone Expander (AU1022), a multi-source LyriQ system can be expanded to support up to 16 zones of audio.

EFFICIENT INSTALLATION

Built on Cat 5 cabling, the LyriQ Audio System includes easy installation features such as convenient RJ45 connections.



LyriQ Keypad (AU7394-XX)

SYSTEM FEATURES

- Up to four sources per multi-source system
- Up to eight zones per multi-source system, with ability to expand
- Whole house control via universal remote and keypad
- High performance and standard systems
- Up to two local source inputs per keypad
- Flush mount inputs in single and triple source versions
- Classic design enhances any décor
- Efficient installation via Cat 5 cabling
- Convenient RJ45 connections



LyriQ Multi-Room Audio System in the Classic Design

AUDIO KITS



AU1006-XX
lyriQ High Performance
Multi-Source, 6-Zone Kit



AU1005-XX
lyriQ High Performance
Multi-Source, 4-Zone Kit



AU1021-XX
lyriQ Multi-Source, 4-Zone Kit
with Flush Mount Inputs




AU1012-XX
lyriQ Single-Source, 4-Zone Kit
with Flush Mount Input


ADDITIONAL PRODUCTS

PRODUCT	PART #	COLOR
lyriQ Multi-Source, 4-Zone Kit	AU1003-XX	Light Almond, White
lyriQ Single Source, 4-Zone Kit	AU7400-XX	Light Almond, White
lyriQ Single Source, 4-Zone Kit with Knobs	AU7395-WH	White
lyriQ High Performance Keypad	AU1000-XX	Black, Ivory, Light Almond, White
lyriQ Keypad	AU7394-XX	Black, Ivory, Light Almond, White
lyriQ Amplified Volume Control	F7399-XX	Ivory, Light Almond, White
lyriQ Local Source Input	F7417-XX	Black, Ivory, Light Almond, White
lyriQ Flush Mount Triple Source Input	AU1011-XX	Black, Light Almond, White
lyriQ Flush Mount Single Source Input	AU1004-XX	Black, Light Almond, White
lyriQ Triple Source Input	F7428	N/A
lyriQ Single Source Input	F7398	N/A
lyriQ Four Source, 8-Zone Distribution Module	AU1002	N/A
lyriQ Single Source, 4-Zone Distribution Module	AU7396	N/A
lyriQ Zone Expander	AU1022	N/A
Home Systems Remote 1060	AU1060	N/A

COLORS



WIRING DIAGRAM



INSTALLATION AT-A-GLANCE: lyriQ SINGLE-SOURCE AUDIO SYSTEM*

1. Run a single Cat 5 cable and speaker wire to each location where a keypad will be installed.
2. Install each keypad in a standard single gang box and connect the Cat 5 cable and a pair of speakers to the keypad.
3. Install the single source distribution module in the On-Q enclosure and connect it to the keypads and source input.
4. Run a Cat 5 cable from the module to the location where the source input will be installed.
5. Install the input in a standard single-gang box and connect the Cat 5.
6. Connect the audio source to the source input.

* Please note that this diagram does not represent a high performance lyriQ system. Diagrams for lyriQ High Performance Audio Systems can be found in our Product Catalog.

301 Fulling Mill Road, Suite G
Middletown, PA 17057
(800) 321-2343



www.legrand.us/onq