






ENTERTAINMENT/lyriQ™ Audio System

lyriQ™ SOURCE INPUTS

PRODUCT	PART #	DESCRIPTION	DIMENSIONS
<p>lyriQ Local Source Input in Studio Design</p>  <p>NEW!</p>	<p>AU5008-GB AU5008-LA AU5008-TI AU5008-WH</p>	<p>The lyriQ Local Source Input enables users to plug in devices like personal audio players locally for in-room entertainment. It includes a convenient RJ45 connection and adjustable gain control. Up to two local source inputs can be installed per zone, and it can be selected from the keypad or the On-Q remote.</p> <p>Includes Studio Wall Plate.</p>	<p>4.2" H x 1.65" W</p>
<p>lyriQ Flush Mount Triple Source Input</p>  <p>NEW!</p>	<p>AU1011-BK AU1011-LA AU1011-WH</p>	<p>The lyriQ Flush Mount Triple Source Input connects to the Four-Source, Eight-Zone Module to distribute three audio sources throughout the home. It features two RJ45 connections, adjustable gain control for each input, three IR emitter ports and one IR target port. Pair with the lyriQ Single Source Input in flush-mount or standard versions (AU1004 or F7398).</p>	<p>4.2" H x 3.3" W</p>
<p>lyriQ Flush Mount Single Source Input</p>  <p>NEW!</p>	<p>AU1004-BK AU1004-LA AU1004-WH</p>	<p>The lyriQ Flush Mount Single Source Input connects to a lyriQ distribution module to distribute one audio source throughout the home. It features an RJ45 connection, adjustable gain control, an IR emitter port and an IR target port.</p>	<p>4.2" H x 1.65" W</p>
<p>lyriQ Triple Source Input</p> 	<p>F7428</p>	<p>The lyriQ Triple Source Input connects to the Four-Source, Eight-Zone Module to distribute three audio sources throughout the home. It features two RJ45 connections, adjustable gain control for each input, three IR emitter ports and one IR target port. Pair with the lyriQ Single Source Input in flush-mount or standard versions (AU1004 or F7398).</p>	<p>2.45" H x 4.5" W x 1.25" D</p>
<p>lyriQ Single Source Input</p> 	<p>F7398</p>	<p>The lyriQ Single Source Input connects to a lyriQ distribution module to distribute one audio source throughout the home. It features an RJ45 connection, adjustable gain control, an IR emitter port and an IR target port.</p>	<p>2.45" H x 4.5" W x 1.25" D</p>
<p>lyriQ Zone Expander</p>  <p>NEW!</p>	<p>AU1022</p>	<p>This new product expands an eight-zone, multi-source lyriQ system to create up to 16 zones of audio. Designed to be connected to two four-source, eight-zone distribution modules, the zone expander includes convenient RJ45 connections and does not require any additional power.</p>	<p>3" H x 6.5" W</p>