

Weatherproof Boxes & Covers Thermoplastic Covers

Pass & Seymour




Weatherproof Boxes & Covers

Thermoplastic Covers


Features

- Broad line of single gang covers for switches, receptacles, GFCIs and power outlets.
- Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).
- Clear polycarbonate lid with reinforced thermoplastic base.


| Catalog Number | Description | Gasket Thickness | 3rd Party Compliance | |
|---|--|------------------|----------------------|-----|
| | | | UL | CSA |
| Self-Closing Covers – Clear Polycarbonate Lid Vertical Two Screw Mounting – Padlockable | | | | |
| 3710 3710WH | Duplex RV use Gray Base/Clear Cover White Base/White Cover | 3/8" | • | • |
| 3720 3720WH | Single Receptacle 1.40" Diameter or Toggle Switch (Toggle Switch Insert Included), Gray Base/Clear Cover White Base/White Cover | 3/8" | • | • |
| 3723 3723WH | Decorator RV use Gray Base/Clear Cover White Base/White Cover | 3/8" | • | • |
| Self-Closing Covers – Clear Polycarbonate Lid Vertical Four Screw Mounting – Padlockable | | | | |
| 3710FS | Duplex Receptacle Gray Base | 3/32" | • | • |
| 3720FS | Single Receptacle 1.40" Diameter or Toggle Switch (Toggle Switch Insert Included), Gray Base | 3/32" | • | • |
| 3723FS | Decorator or GFCI Gray Base | 3/32" | • | • |
| 3722FS | Power Outlet, 1.60" Diameter Gray Base | 3/32" | • | • |
| 3724FS | Power Outlet, 1.73" Diameter Gray Base | 3/32" | • | • |
| 3795 | Power Outlet, 2.13" Diameter Gray Base | 3/8" | • | • |
| Self-Closing Covers – Clear Polycarbonate Lid Horizontal Two Screw Mounting | | | | |
| 3700 | Duplex Receptacle Gray Base | 3/32" | • | • |
| 3703 | Decorator Gray Base | 3/32" | • | • |
| 3703T | Decorator RV Use Gray Base | 3/8" | • | • |
| 3703TCW | Decorator RV Use Colonial White Base | 3/8" | • | • |
| Self-Closing Covers – Clear Polycarbonate Lid Horizontal Four Screw Mounting | | | | |
| 3700FS | Duplex Receptacle Gray Base | 3/32" | • | • |
| 3703FS | Decorator Receptacle Gray Base | 3/32" | • | • |




3720FS




3723FS



3710



3700



3703