
Pass & Seymour

□ legrand







885TR-LA



TM8HWLTR-LACC

2 Pole, 3 Wire



Straight Blade Devices TradeMaster® Decorator TamperResistant & Combination Receptacles

15A, 125V

Features

- High impact-resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Tri-drive screws.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.

- Side wire accepts #12 #14 AWG solid.
- Push wire accepts #14 AWG solid only.
- UL Listed as tamper-resistant to prevent improper insertion of foreign objects per UI 498
- Specially designed for increased protection of children in their homes.
- Superior protection than traditional outlet "caps" or "protection plates".

					3rd Party Compliance			
Catalog Number	Rat A.	ing V.	Color	NEMA Config. No.	cULus	UL UL498		
Decorator Tamper-Resistant Receptacles								
885TR-I	15	125	lvory	5-15R	•	•		
885TR-W	15	125	White	5-15R	•	•		
885TR-BK	15	125	Black	5-15R	•	•		
885TR-LA	15	125	Light Almond	5-15R	•	•		

Features

- Impact-resistant face and body.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- GE Lexan[™] high impact-resistant lens.
- Tri-drive screws.
- Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.
- Sensor automatically turns light ON in the dark.
- Increased light output for better illumination.
- Light sensor for enhanced sensitivity.
- UL tested shutter mechanism for protection against improper object insertion per UL498.
- Specially designed for increased protection of children in their homes.
- Superior protection than traditional outlet "caps" or "protection plates.

					3rd Party Compliance					
Catalog Number	Rating A. VAC	Light Output in 1' FCD*	Color	NEMA Config. No.	c. ULus UL498					
Decorator Hallway Light with High Output Light & Tamper-Resistant Single Receptacle										
TM8HWLTR-ICC	15 125	0.2561	Ivory	5-15R	•					
TM8HWLTR-WCC	15 125	0.2561	White	5-15R	•					
TM8HWLTR-BKCC	15 125	0.2561	Black	5-15R	•					
TM8HWLTR-CC	15 125	0.2561	Brown	5-15R	•					
TM8HWLTR-LACC	15 125	0.2561	Light Almond	5-15R	•					

^{*} FCD = Foot Candle Distance, 1 Lumen = 1 FCD. See Page U-42 for more information.

For complete line of Decorator Combination Devices and Hallway Lights, see Pages D-6 – D-10, D-17, D-19, D-25, and D-26.