

Switches TradeMaster® Decorator Combination Switches


15A, 120VAC

Pass & Seymour




Features


- Impact-resistant face and body.
- Fully rounded back body protects wires from being damaged by sharp edges.
- Clear identification of circuits.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Ground screw position under the end of the strap minimizes the risk of contact.
- Full wraparound metal strap with lock-in tabs.
- Patented split circuit tab – easily accessible, and can be reinstalled without a tool.
- Unique “Up/Down” switches match the look and feel of standard Decorator switches.
- Largest breadth of 15 amp offering.
- All screws are tri-drive.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects (see Page A-22).



TM811WCC



TM8111WCC



TM81111WCC

All devices listed on this page conform to NEMA WD-1 and WD-6.

Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			UL [®] UL20	cUL [®] _{us}
Two Single Pole Switches				
TM811ICC	15 120	Ivory	•	•
TM811WCC	15 120	White	•	•
TM811CC	15 120	Brown	•	•
TM811BKCC	15 120	Black	•	•
TM811LACC	15 120	Light Almond	•	•
Two Single Pole Switches with Pilot Light				
TM811PLICC	15 120	Ivory	•	•
TM811PLWCC	15 120	White	•	•
TM811PLBKCC	15 120	Black	•	•
TM811PLLACC	15 120	Light Almond	•	•
Single Pole Switch & Three-Way Switch				
TM813ICC	15 120	Ivory	•	•
TM813WCC	15 120	White	•	•
TM813CC	15 120	Brown	•	•
TM813BKCC	15 120	Black	•	•
TM813LACC	15 120	Light Almond	•	•
Single Pole Switch with Pilot Light & Three-Way Switch				
TM813PLICC	15 120	Ivory	•	•
TM813PLWCC	15 120	White	•	•
TM813PLBKCC	15 120	Black	•	•
TM813PLLACC	15 120	Light Almond	•	•
Two Three-Way Switches				
TM833ICC	15 120	Ivory	•	•
TM833WCC	15 120	White	•	•
TM833CC	15 120	Brown	•	•
TM833BKCC	15 120	Black	•	•
TM833LACC	15 120	Light Almond	•	•
Three Single Pole Switches				
TM8111ICC	15 120	Ivory	•	•
TM8111WCC	15 120	White	•	•
TM8111CC	15 120	Brown	•	•
TM8111BKCC	15 120	Black	•	•
TM8111LACC	15 120	Light Almond	•	•
Two Single Pole Switches & Three-Way Switch				
TM8113ICC	15 120	Ivory	•	•
TM8113WCC	15 120	White	•	•
TM8113CC	15 120	Brown	•	•
TM8113BKCC	15 120	Black	•	•
TM8113LACC	15 120	Light Almond	•	•
Four Single Pole Switches				
TM81111ICC	15 120	Ivory	•	•
TM81111WCC	15 120	White	•	•
TM81111CC	15 120	Brown	•	•
TM81111BKCC	15 120	Black	•	•
TM81111LACC	15 120	Light Almond	•	•