


Pass & Seymour




Switches

TradeMaster® Decorator Combination Switches


15A, 120/125VAC



TM818TRWCC



TM818WCC



TM8118TRWCC

NEW

Tamper-Resistant Single Pole Switch & Single Receptacle

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				UL20	UL498	cULus
TM818TRICC	15 120/125	Ivory	5-15R	•	•	•
TM818TRWCC	15 120/125	White	5-15R	•	•	•
TM818TRCC	15 120/125	Brown	5-15R	•	•	•
TM818TRBKCC	15 120/125	Black	5-15R	•	•	•
TM818TRLACC	15 120/125	Light Almond	5-15R	•	•	•

NEW

Tamper-Resistant Single Pole Switch & Single Receptacle with Pilot Light

TM818TRPLICC	15 120/125	Ivory	5-15R	•	•	•
TM818TRPLWCC	15 120/125	White	5-15R	•	•	•
TM818TRPLBKCC	15 120/125	Black	5-15R	•	•	•
TM818TRPLLACC	15 120/125	Light Almond	5-15R	•	•	•

NEW

Tamper-Resistant Three-Way Switch & Single Receptacle

TM838TRICC	15 120/125	Ivory	5-15R	•	•	•
TM838TRWCC	15 120/125	White	5-15R	•	•	•
TM838TRCC	15 120/125	Brown	5-15R	•	•	•
TM838TRBKCC	15 120/125	Black	5-15R	•	•	•
TM838TRLACC	15 120/125	Light Almond	5-15R	•	•	•

NEW

Tamper-Resistant Two Single Pole Switches & Single Receptacle

TM8118TRICC	15 120/125	Ivory	5-15R	•	•	•
TM8118TRWCC	15 120/125	White	5-15R	•	•	•
TM8118TRCC	15 120/125	Brown	5-15R	•	•	•
TM8118TRBKCC	15 120/125	Black	5-15R	•	•	•
TM8118TRLACC	15 120/125	Light Almond	5-15R	•	•	•

Single Pole Switch & Single Receptacle

TM818ICC	15 120/125	Ivory	5-15R	•	•	•
TM818WCC	15 120/125	White	5-15R	•	•	•
TM818CC	15 120/125	Brown	5-15R	•	•	•
TM818BKCC	15 120/125	Black	5-15R	•	•	•
TM818LACC	15 120/125	Light Almond	5-15R	•	•	•

Single Pole Switch & Single Receptacle with Pilot Light

TM818PLICC	15 120/125	Ivory	5-15R	•	•	•
TM818PLWCC	15 120/125	White	5-15R	•	•	•
TM818PLBKCC	15 120/125	Black	5-15R	•	•	•
TM818PLLACC	15 120/125	Light Almond	5-15R	•	•	•

Three-Way Switch & Single Receptacle

TM838ICC	15 120/125	Ivory	5-15R	•	•	•
TM838WCC	15 120/125	White	5-15R	•	•	•
TM838CC	15 120/125	Brown	5-15R	•	•	•
TM838BKCC	15 120/125	Black	5-15R	•	•	•
TM838LACC	15 120/125	Light Almond	5-15R	•	•	•

Two Single Pole Switches & Single Receptacle

TM8118ICC	15 120/125	Ivory	5-15R	•	•	•
TM8118WCC	15 120/125	White	5-15R	•	•	•
TM8118CC	15 120/125	Brown	5-15R	•	•	•
TM8118BKCC	15 120/125	Black	5-15R	•	•	•
TM8118LACC	15 120/125	Light Almond	5-15R	•	•	•

Single Pole Switch & Pilot Light

TM81PLICC	15 120/125	Ivory		•	•	•
TM81PLWCC	15 120/125	White		•	•	•
TM81PLBKCC	15 120/125	Black		•	•	•
TM81PLLACC	15 120/125	Light Almond		•	•	•

Three-Way Switch & Pilot Light

TM83PLICC	15 120/125	Ivory		•	•	•
TM83PLWCC	15 120/125	White		•	•	•
TM83PLBKCC	15 120/125	Black		•	•	•
TM83PLLACC	15 120/125	Light Almond		•	•	•