








# Weatherproof Boxes & Covers While-In-Use Covers


Pass & Seymour  
**legrand**

## Features


- Comply with NEC 2002 Section 406.8(B)(1) for wet location covers, and conform to NEMA 3R.
- Covers are self-closing as required by UL514C42.3.
- Covers mount vertically or horizontally.
- Body, cover and plates made of polycarbonate.
- Gasket made of closed cell foam, neoprene blend regular density, UL Rated HBF.
- Mounting screws made of 302 stainless steel.
- Single receptacle plate available in 1.405" and 1.595" openings.
- Deep model available for 20A locking plugs.
- Shallow covers accommodate up to 14/3 AWG extension cords.
- New trigger latch opens easily with one finger.

Catalog Number	Color	Device Plates Provided	Plate Width	Package Quantity	3rd Party Compliance
					
<b>Single Gang</b>					
WIUC10-GL WIUC10-CL WIUC10-WL	Gray Clear White		2 3/8"	12	•
<b>Single Gang Shallow</b>					
WIUC10-SG WIUC10-SC WIUC10-SW	Gray Clear White		2 3/8"	14	•
<b>Single Gang Deep</b>					
WIUC10-DGL WIUC10-DCL WIUC10-DWL	Gray Clear White		2 3/8"	9	•
<b>Two Gang</b>					
WIUC20-GL WIUC20-CL WIUC20-WL	Gray Clear White		2"	8	•
<b>Extra Plate Kits</b>					
WIU10-PK WIU10-PKW	Gray White	Single Gang Plate Kit 	2 3/8"		•
WIU20-PK WIU20-PKW	Gray White	Two Gang Plate Kit 	2"		•


SINGLE GANG,  
SINGLE GANG SHALLOW,  
SINGLE GANG DEEP  
COVERS




SINGLE GANG  
COVER





SINGLE GANG  
SHALLOW COVER



SINGLE GANG  
DEEP COVER



TWO GANG COVER



# Weatherproof Boxes & Covers

**Two sizes: 1.96" and 2.32" diameters,** to cover 15A/20A Straight Blade and 15A/20A/30A Turnlok® devices. Covers fit all competitive flanged inlets and outlets.

**Tamper-proof hinge** features permanent, locked-in pins for added security.

**Unbreakable glass-filled polycarbonate construction** withstands years of job site abuse and harsh environmental exposure. Stainless steel mounting screws resist corrosion.


**Stainless steel mounting screws** resist corrosion.



**WPG-1 and WPG-2**

**Pre-attached gaskets** for easy installation and tight seal to panel or weatherproof box — with no misaligned or collapsed gaskets.

**Lockable "bullnose"** for OSHA Lockout/Tagout compliance.



**Molded-in label area** for pre-printed or handwritten labels identifying circuits, ratings, and other data.

**We offer a complete line of durable, easy-to-install, and environment-resistant weatherproof products — for first-rate performance in worst-case applications.**

## Index

Device	Page Number
While-In-Use Covers	Q-2, Q-3
Cast Weatherproof Covers	Q-4 – Q-6
Thermoplastic Covers	Q-7 – Q-10
Heavy Cast Aluminum Covers	Q-10, Q-11
Single Gang Boxes	Q-13
Two Gang Boxes	Q-14
Three Gang Boxes & Deep Boxes	Q-15
Round Boxes & Swimming Pool Junction Box	Q-16
Cluster & Blank Covers	Q-17
Weatherproof Stainless Steel Covers	Q-18
Lighting Accessories	Q-19
Vapor Proof Lighting	Q-20
Gaskets & Accessories	Q-21
NEC Compliance	Q-22