





## FITTINGS FOR 7500 PANCAKE OVERFLOOR STEEL RACEWAY

Unpainted [Galvanized Finish]



### 1546A\* SINGLE RECEPTACLE BOX

Will accommodate commercially available straight blade and locking single receptacles with face diameters of 1.38-1.40" [35-36mm]. Base has 1/2" [12.7mm] and 3/4" [19.1mm] trade size concentric KOs. Cover has 1500 and 2600 twistouts on all four sides. Two 1500WC Wire Clips included. **Gray finish.**





### 1546B\* DUPLEX RECEPTACLE BOX

Will accommodate commercially available 15A or 20A duplex receptacles. Base has 1/2" [12.7mm] and 3/4" [19.1mm] concentric trade size KOs. Cover has 1500 and 2600 twistouts on all four sides. Two 1500WC Wire Clips included. Side wiring recommended. **Gray finish.**





### 1546T TELEPHONE OUTLET BOX

Furnished with 1/2" [12.7mm] rubber stem. Designed to accept modular connecting blocks within the fitting. Cover has 1500 and 2600 twistouts on both ends and both sides. Two 1500WC Wire Clips included. Not LJJ Listed. **Gray finish.**



### 1585 COMBINATION CONNECTOR

For connecting 1/2" [12.7mm] trade size conduit or armored cable to Pancake 1500.



 Add C prefix to denote Canadian version — Agency approved for sale in Canada.   
NOTE: Box covers are manufactured of UL Listed Noryl plastic, gray textured finish.



# FEATURES & BENEFITS

## PANCAKE OVERFLOOR STEEL RACEWAY 1500

- **Brings power or telephone and signal wiring to away-from-wall locations without channeling into floor surface.** Speeds installation.
- **Flat profile.** Unobtrusive appearance.
- **Unpainted galvanized steel.** Assures durability.
- **Withstands approximately 200 lbs./sq. in.** Provides safe load-bearing strength for normal office traffic.
- **Full line of fittings for distribution of receptacle or telephone outlets from perimeter wiring to desk locations in the office core.** Provides a complete installation. Minimizes inventory requirements.

### CODE REFERENCE



UL Listed  
**Raceway:**

I R1eE4376  
Guide RJBT

! **Fittings:**  
- File 41751  
Guide RJPH

**Meets Article**  
**352A**  
of NEC.

**GSA Certified**  
**Raceway:**

File 35D  
**Meets Section**  
**12-1600**  
of CEC.

*NOTE: See page T1•3 for additional National Electrical Code (NEC) Articles pertinent to use of these products.*

K1 • 3

**K1**

**1500 / 2600 PANCAKE OVERFLOOR STEEL RACEWAY**