


WALL PLATES, INSERTS & ENCLOSURES GUIDE




designed to be better.™



SUPERIOR INFRASTRUCTURE SOLUTIONS



CONNECTIVITY




As the industry leader in structured wiring, On-Q® provides the proven, practical solutions preferred by installers and major home builders across the country. Our comprehensive product offering — which includes wall plates, jacks, straps, tools, modules and enclosures — simplifies installations and reduces time on site. We specialize in meeting the right specifications for any project — residential or light commercial — with solutions that exceed your needs. From single-family homes to apartments, townhomes to condominiums, On-Q has the professional answer for any project.

HDMI

This full line of CL-3 in-wall UL-rated HDMI High-Speed with Ethernet products — which includes cables, couplers, repeaters and extenders — deliver an unparalleled HD audio and video experience.





WALLPLATES & INSERTS

Our line of Keystone wall plates and Cat 5e, Cat6, Cat6a, F-Connectors, speaker binding posts and RCA inserts provide flexible setup options at any location.

DECORATOR STRAPS

We offer a series of pre-configured outlet straps for data, phone, video and home theater applications. Add a home theater strap to enable HD audio and video with a few simple connections, or quickly wire a home office using our pre-configured outlet straps that combine phone, data and video into a single decorator opening.

ENCLOSURES

Our durable enclosures range in size from 12 to 42 inches to suit any installation. Every enclosure is made in the USA and is compatible with all major module mounting schemes. They offer three 2.5" top openings for high capacity projects, side lances and side tabs for more flexible installation options. Available with hinged or screw-on doors, a Legrand enclosure is the easy choice for professional projects.



WALL PLATES

KEYSTONE WALL PLATES



WP3401-WH*



WP3402-WH*



WP3403-WH



WP3404-WH



WP3406-WH



WP3212-WH



WP1194-WH

*Available in packs of 25

PART NO.	DESCRIPTION
WP3401-XX (KTPD1-XX)	1-Gang, 1-Port Wall Plate 25 Count Bulk Pack in WH or LA (WP3401-XX-25)
WP3402-XX (KTPD2-XX)	1-Gang, 2-Port Wall Plate 25 Count Bulk Pack in WH or LA (WP3402-XX-25)
WP3403-XX (KTPD3-XX)	1-Gang, 3-Port Wall Plate
WP3404-XX (KTPD4-XX)	1-Gang, 4-Port Wall Plate
WP3406-XX (KTPD6-XX)	1-Gang, 6-Port Wall Plate
WP3212-XX	2-Gang, 12-Port Wall Plate Colors: IV, LA and WH
WP1194-XX	1-Gang, Blank Wall Plate

COLORS: BK, BR, IV, LA, WH
DIMENSIONS: 1-GANG: 2.9375" x 4.6875" 2-GANG: 4.75" x 4.6875"

KEYSTONE LABELED Wall Plates

PART NO.	DESCRIPTION
KTPDL1-XX	1-Port Keystone Labeled Wall Plate
KTPDL2-XX	2-Port Keystone Labeled Wall Plate
KTPDL3-XX	3-Port Keystone Labeled Wall Plate
KTPDL4-XX	4-Port Keystone Labeled Wall Plate
KTPDL6-XX	6-Port Keystone Labeled Wall Plate

COLORS: IV, LA, WH DIMENSIONS: 1-GANG: 2.9375" x 4.6875" 2-GANG: 4.75" x 4.6875"

OVERSIZED WALL PLATES



WP3301-WH



WP3302-WH



WP3303-WH



WP3304-WH



WP3306-WH



WP3300-WH

PART NO.	DESCRIPTION
WP3301-XX	1-Gang, 1-Port Oversized Wall Plate
WP3302-XX	1-Gang, 2-Port Oversized Wall Plate
WP3303-XX	1-Gang, 3-Port Oversized Wall Plate
WP3304-XX	1-Gang, 4-Port Oversized Wall Plate
WP3306-XX	1-Gang, 6-Port Oversized Wall Plate
WP3300-XX	1-Gang, Blank Oversized Wall Plate

COLORS: WH, LA
DIMENSIONS: 1-GANG: 3.3125" x 5.0625" 2-GANG: 5.125" x 5.0625"
3-GANG: 6.9375" x 5.0625" 4-GANG: 8.75" x 5.0625"

COLOR OPTIONS



WALL PLATES & LOW VOLTAGE BRACKETS

DECORATOR WALL PLATES




TP13-WH



TP26-WH



TP262-WH



TP263-WH



TP264-WH

PART NO.	DESCRIPTION
TP13-XX (WP1194-XX)	1-Gang Blank Wall Plate
TP26-XX (WP1205-XX)	1-Gang Decorator Wall Plate
TP262-XX (WP1207-XX)	2-Gang Decorator Wall Plate
TP263-XX (WP1208-XX)	3-Gang Decorator Wall Plate
TP264-XX	4-Gang Decorator Wall Plate

COLORS:

BK, BR, IV, LA, WH

DIMENSIONS:

1-GANG: 2.9375" x 4.6875"

2-GANG: 4.75" x 4.6875"

JUMBO DECORATOR Wall Plates

PART NO.	DESCRIPTION
TPJ13-XX	Jumbo 1-Gang Blank Wall Plate
TPJ26-XX	Jumbo 1-Gang Wall Plate
TPJ262-XX	Jumbo 2-Gang Wall Plate
TPJ263-XX	Jumbo 3-Gang Wall Plate

COLORS:

BK, BR, IV, LA, WH

DIMENSIONS:

1-GANG: 3.3125" X 5.0625", 2-GANG: 5.125" X 5.0625", 3-GANG: 6.9375" X 5.0625"

LOW VOLTAGE BRACKETS



AC1009-01



AC1009-02



AC1009-11



AC1010-01



AC1010-02



AC1010-03

PART NO.	DESCRIPTION
AC1009-01	1-Gang, LV Bracket w/Nail, New Construction
AC1009-02	2-Gang, LV Bracket, Face Mount, New
AC1009-11	1-Gang, LV Bracket, Face Mount, New
AC1010-01	1-Gang, LV Bracket, Retrofit
AC1010-02	2-Gang, LV Bracket, Retrofit
AC1010-03	3-Gang, LV Bracket, Retrofit

CRAFTED WITH DURABLE HEAVY-DUTY PLASTIC, ON-Q LV BRACKETS FEATURE AN OPEN BACK AND AN INTEGRATED CABLE MANAGEMENT SYSTEM FOR CLEAN CONNECTIONS AND EASY INSTALLATION

COLOR OPTIONS

