













DS4000 Series Raceway Fittings Ordering Information (continued)

Catalog No./Item	Description/Specifications
<p>DS4010A-DV DS4010A-BK DS4010A-DG DS4010A-BZ</p>	<p>Entrance End Fitting – Full-capacity end fitting. Includes four 3/4" and 1 1/4" concentric trade size KOs and four 2 1/8" large capacity KOs.</p> 
<p>DS4010B-DV DS4010B-BK DS4010B-DG DS4010B-BZ</p>	<p>Blank End Fitting – For closing open end of DS4000B Raceway Base. Has two 3/4" and 1" trade size KOs.</p> 
<p>DS4011-DV DS4011-BK DS4011-DG DS4011-BZ</p>	<p>Flat Elbow – 90° flat corner for new lay-in or pull-through installations.</p> 
<p>DS4014A</p>	<p>Backfeed Coupling – Extra long coupling allows attachment to wall box or back fed 1" or 1 1/4" trade size conduit.</p> 
<p>DS4015-DV DS4015-BK DS4015-DG DS4015-BZ</p>	<p>Divided Tee Fitting – For new lay-in or pull-through installations.</p> 
<p>DS4017-DV DS4017-BK DS4017-DG DS4017-BZ</p>	<p>Internal Elbow – 90° internal corner for new installations. Flexible base conforms to out-of-square corners.</p> 
<p>DS4018-DV DS4018-BK DS4018-DG DS4018-BZ</p>	<p>External Elbow – 90° external corner for new lay-in or pull-through installations. Flexible base conforms to out-of-square corners.</p> 
<p>DS4047D-DV DS4047D-BK DS4047D-DG DS4047D-BZ</p>	<p>Single Channel Duplex Device Plate – For 15A and 20A duplex receptacles or 106 style data frames.</p> 
<p>DS4047DQ-DV DS4047DQ-BK DS4047DQ-DG DS4047DQ-BZ</p>	<p>Single Channel Duplex Device Plate w/One Duplex Installed – Includes one Pass & Seymour 20A duplex receptacle with 6" [152mm] lead wires installed on bracket.</p> 
<p>DS4047R-DV DS4047R-BK DS4047R-DG DS4047R-BZ</p>	<p>Single Channel Decorator Device Plate – For 15A and 20A duplex receptacles, or 106 style data frames.</p> 
<p>DS4047MAB-DV DS4047MAB-BK DS4047MAB-DG DS4047MAB-BZ</p>	<p>Single Channel MAB Device Plate – For all communication devices, including mini adapter bezels.</p> 
<p>DS4047C-DV DS4047C-BK DS4047C-DG DS4047C-BZ</p>	<p>Single Channel NEMA Device Plate – Use with commercially-available flush plates.</p> 

ORT
P&S
OPEN

NOTE: “-DV” suffix indicates Designer Ivory color, “-DG” suffix indicates Designer Gray color, “-BK” suffix indicates Matte Black color, and “-BZ” suffix indicates Metallic Bronze color.

WIREMOLD


legrand®

4000 Designer Series™ Steel Raceway

Innovative Raceway Profile Provides Increased Wiring Capacity

Available Factory Prewired

NEW!



Introducing the next generation in innovative surface raceway systems. The new 4000 Designer Series™ Raceway from Wiremold/Legrand provides an aesthetically and functionally superior alternative to existing raceway profiles. DS4000™ Series Raceway includes a variety of innovative features and fittings that save installation time, cost less to specify, and provide 1/3 more wiring capacity than conventional box-style raceway profiles.

DS4000™ Series Raceway is a dual service steel raceway, with twin covers and a built-in divider that provides full isolation of services. With its increased capacity and unique downward-facing activation capabilities, DS4000™ Series Raceway is ideal for any commercial, institutional, or industrial application requiring a high capacity metal raceway.



DS4000™ Raceway in a contemporary office environment.



Sectioned view illustrating internal crossover capability, allowing adjacent downward facing power and data activations. Raceway profile meets or exceeds EIA/TIA bend radius requirements.



DS4000™ Series Raceway prewired with streamlined downward facing power and data activations.