


## F Series Single Gang Boxes

Outside Dimensions:

Height,  $4\frac{9}{16}$ " – Width,  $2\frac{13}{16}$ " – Depth 2", Cubic Inches = 25.67



Size (in)	Part Number	Product Code
1/2	FSC10	077607
3/4	FSC15	077608
1/2	FS10	077601
3/4	FS15	077602
1/2	FSCC10	077622
3/4	FSCC15	077623
1/2	FSS10	077604
3/4	FSS15	077605


Note: 10 = 1/2" Hub, 15 = 3/4" Hub

## FD Series Single Gang Deep Boxes

Outside Dimensions:

Height,  $4\frac{9}{16}$ " – Width,  $2\frac{13}{16}$ " – Depth  $2\frac{3}{4}$ ", Cubic Inches = 35.30

With the exception of the FD Blank Box, Scepter FD Series Single Gang Deep Boxes are molded with 1" conduit hubs and supplied with reducer bushings. The conduit hub(s) are field modified as 1/2", 3/4" or 1" to accommodate job-site requirements. The appropriate quantity of 1" x 3/4" and 3/4" x 1/2" reducers to create the desired hub size are packaged with each FD Series Single Gang Deep Box.




Size (in)	Part Number	Product Code
1/2, 3/4, 1	FDC101520	077291
1/2, 3/4, 1	FDS101520	077299
BLANK	FD BLANK	077603
347 VOLT	FD347	077610

## F Series Double Gang Boxes

FS-2 cu.in = 39.5, FSC-2 & FSS-2 cu.in. = 37.0, FSCC-2 cu.in.= 36.0

Hub Size (in)	Part Number	Product Code	OD (inches)		
			H	W	D
1/2, 3/4, 1	FS-2-101520	077440	4.5	4.75	2.5
1/2, 3/4, 1	FSC-2-101520	077441	4.5	4.75	2.5
1/2, 3/4, 1	FSS-2-101520	077442	4.5	4.75	2.5
1/2, 3/4, 1	FSCC-2-101520	077443	4.5	4.75	2.5
Blank	FD-2	077734	4.75	4.75	3.0



## F Series Triple Gang Boxes

Hub Size (in)	Part Number	Product Code	OD (inches)		
			H	W	D
1/2, 3/4, 1	FS-3-101520	077337	4.5	6.6	2.5
1/2, 3/4, 1	FSC-3-101520	077438	4.5	6.6	2.5
Blank	FD-3	077737	4.5	6.6	3.0

Note: All F series boxes are supplied with integral mounting feet, threaded brass inserts and grounding clips.

