



Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

TRAC-MASTER®

Classics STEP CYLINDERS

T303, T305 and T307

PRODUCT DESCRIPTION

Step Cylinders combine contemporary styling with quality metallic and enamel finishes.

Construction Drawn steel housing with polycarbonate stem.

Lampholder Medium base porcelain with nickel plated copper screw shell.

Aiming 90° vertical aiming capability and 358° rotation.

Adapter Copper alloy contacts provide precise spring action - no arcing and will not take a set • True, positive electrical ground • On/off switch included • Patented embossed polarity arrows on bottom of adapter • Spring-loaded positive latch with embossed polarity arrows secures trac light to trac • "Pull-up" contact to up position for two-circuit application.

Labels UL listed, CSA certified.

Product specifications subject to change without notice.



Line Voltage R20


Catalog Number	Finish	Baffle	Lamp
T303B-WH	White	Black	27-50W R20/35-50W PAR20
T303B-BL	Black	Black	27-50W R20/35-50W PAR20
T303W-WH	White	White	27-50W R20/35-50W PAR20

ACCESSORIES

Cat. No.	Description	Cat. No.	Description	Cat. No.	Description
T71BL	Black Barn Doors †	T560BL	Black Accessory Holder	T561-6	Color Filters
T569BL	Cube Cell Louver	T5677	Prismatic Spread Lens	T5678	Linear Spread Lens
T5621	Uniformity Lens	T5622	UV Filter	T5618	Color Correction Filter

See specification sheet [D1.2.2](#) for details.

† Barn Doors accept Color Filters, Lenses and Louvers.



Line Voltage BR30/PAR30L


Catalog Number	Finish	Baffle	Lamp
T305B-WH	White	Black	45-75W BR30/35-75W PAR30L
T305B-BL	Black	Black	45-75W BR30/35-75W PAR30L
T305W-WH	White	White	45-75W BR30/35-75W PAR30L

ACCESSORIES

Cat. No.	Description	Cat. No.	Description	Cat. No.	Description
T72BL	Black Barn Doors †	T570BL	Black Accessory Holder	T571-6	Color Filters
T579BL	Cube Cell Louver	T5777	Prismatic Spread Lens	T5778	Linear Spread Lens
T5721	Uniformity Lens	T5722	UV Filter	T5718	Color Correction Filter

See specification sheet [D1.2.2](#) for details.

† Barn Doors accept Color Filters, Lenses and Louvers.



TRAC-MASTER®

Classics

STEP CYLINDERS**T303, T305 and T307****Line Voltage PAR38/BR40**

Steel yoke, one locking knob provided.

Catalog Number	Finish	Baffle	Lamp
T307B-WH	White	Black	45-150W PAR38 or 65-120W BR40
T307B-BL	Black	Black	45-150W PAR38 or 65-120W BR40

ACCESSORIES

Cat. No.	Description	Cat. No.	Description	Cat. No.	Description
T73BL	Black Barn Doors†	T73WH	White Barn Doors†	T580BL	Black Accessory Holder
T581-6	Color Filters	T589BL	Cube Cell Louver		

See specification sheet [D1.2.2](#) for details.

† Barn Doors accept Color Filters, Lenses and Louvers.

