

5" LED Downlight Ordering Information

For new construction or remodeling, you can add energy-efficient LED lighting from Juno. 5" housing is compatible with a variety of trims to complement virtually any design.

5" New Construction



IC20LED

Dedicated 5" LED new construction housing with integral 14W nominal light engine and universal 120V-277V driver. Air-Loc fully sealed housing does not require separate gasket. IC housing designed for use in IC or non-IC construction.

16 1/8" L x 9 1/8" W x 7 1/2" H
Ceiling Cutout: 5 5/8"

IC20LED-3K

IC20SLED-3K (Smaller footprint bar hanger Real Nail® 2)
3000K LED color temperature

IC20LED-35K

IC20SLED-35K (Smaller footprint bar hanger Real Nail® 2)
3500K LED color temperature

IC20LED-41K

IC20SLED-41K (Smaller footprint bar hanger Real Nail® 2)
4100K LED color temperature

5" Remodel



IC20RLED

Dedicated 5" LED remodel housing with integral 14W nominal light engine and universal 120V-277V driver. Air-Loc gasket kit supplied with housing. IC housing designed for use in IC or non-IC construction.

12 7/8" L x 5 7/8" W x 7 5/8" H
Ceiling Cutout: 5 1/2"

IC20RLED-3K

3000K LED color temperature

IC20RLED-35K

3500K LED color temperature

IC20RLED-41K

4100K LED color temperature

Qualified Dimmers - 120V

Juno LED downlights have been qualified for use with the following 120V electronic low voltage dimmers. These dimmers require a neutral wire in the wall box.

Mfg: Lutron
Model #'s: SKYLARK® SELV-303P
SKYLARK® SELV-300P
NOVA T☆® NTELV-600
NOVA T☆® NTELV-300
DIVA® DVELV-300P

Mfg: Leviton
Model #: ACENTI® ACE06-1LW
MONET® MNE04-1LW
VIZIA+® VPE04-1LZ
VIZIA+® VZE04-1LX

Consult Juno technical services for the most up to date list of qualified dimmers.

5" LED Downlight Trims

Downlights



Downlight Baffle

205W-WH White
205B-WH Black
205B-SC Black
205B-ABZ Black



Downlight Cone

204C-WH Clear Alzak
204G-WH Gold Alzak
204B-WH Black Alzak
204PT-SC Pewter Alzak
204W-WH Gloss White
204HZ-WH Haze
204WHZ-WH Wheat Haze
204WHZ-ABZ Wheat Haze

Lensed



Flat Glass Shower Trim*

210-ABZ
210-SC
210-WH



Frosted Lens with Clear Center*

212-ABZ
212-SC
212-WH



White Baffle, Regressed Frosted Dome Lens*

2130W-WH
2130B-WH



Beveled Frame, Frosted Dome Lens*

5101-ABZ
5101-SC
5101-WH

*Do not use reflector shipped with trim for LED housing. Discard or recycle reflector.

Trim Finishes

ABZ – Classic Aged Bronze
SC – Satin Chrome
WH – White