

PASS & SEYMOUR®

SELF-TEST GFCI WITH SAFELOCK® PROTECTION



THE GFCI THAT SELF-TESTS EVERY THREE SECONDS.



1597TRW

We've reset the bar
on electrical safety.

When it comes to electricity in the home, safety is of the utmost importance. That's why we've created the first GFCI receptacle that ensures continuous protection by self-testing every three seconds.

Far surpassing 2015 UL safety standards, it also features our patented SafeLock Protection: if critical components are damaged and protection is lost, power to the receptacle will be disconnected.

In addition to these important safety enhancements, the new P&S Self-Test GFCI Receptacle also features a thinner profile that leaves more room for wires in the wall box. That means it's not only the safest GFCI receptacle available but the easiest to install as well.

designed to be better.™

 **legrand**®

Self-Test GFCI with SafeLock®

Protection — conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

Meets 2015 UL requirements

Prevents line-load reversal miswire — no power to the face or downstream receptacles if wired incorrectly.

FSUL Listed (Federal Specification WC596)

Auto-ground clip assures a positive ground to metal box.



Thinner profile speeds installation by leaving more room for wires in the box.

Tamper-Resistant — Automatic shutter system prevents young children from inserting common household objects such as hairpins or keys.

Indicator light makes it easy to identify status.

The most durable GFCI receptacle available — Exceeds UL943 voltage surge requirements; survives 100X the required UL 3kA/6kV voltage surge test cycles.

High-impact-resistant, thermoplastic construction for superior strength and durability.

PART NO.	DESCRIPTION	RATINGS		COLORS	NEMA Config.
		A.	V.		
1597*	TradeMaster® Duplex Self-Test GFCI	15	125	I, LA, W, GRY, BK, RED, -	5-15R
1597TR*	TradeMaster® Tamper-Resistant Duplex Self-Test GFCI	15	125	I, LA, W, BK, -	5-15R
1597TRWR*	TradeMaster® Tamper-Resistant Weather-Resistant Duplex Self-Test GFCI	15	125	I, LA, W, GRY, BK, -	5-15R
2097*	Spec Grade Duplex Self-Test GFCI	20	125	I, LA, W, GRY, BK, RED, -	5-20R
2097TR*	Spec Grade Tamper-Resistant Duplex Self-Test GFCI	20	125	I, LA, W, GRY, BK, RED, -	5-20R
2097TRWR*	TradeMaster® Tamper-Resistant Weather-Resistant Duplex Self-Test GFCI	20	125	I, LA, W, GRY, BK, -	5-20R
1597HG*	Hospital Grade Duplex Self-Test GFCI	15	125	I, LA, W, GRY, BK, RED, -	5-15R
1597HGTR*	Hospital Grade Tamper-Resistant Duplex Self-Test GFCI	15	125	I, LA, W, GRY, BK, RED, -	5-15R
2097HG*	Hospital Grade Duplex Self-Test GFCI	20	125	I, LA, W, GRY, BK, RED, -	5-20R
2097HGTR*	Hospital Grade Tamper-Resistant Duplex Self-Test GFCI	20	125	I, LA, W, GRY, BK, RED, -	5-20R
2087*	TradeMaster® Dead Front Self-Test GFCI	20	125	I, LA, W, BK	n/a

*COLOR DESIGNATION

W	White
I	Ivory
BK	Black
LA	Light Almond
-	Brown
GRY	Gray
RED	Red

All GFCIs are Fed Spec, FSUL Listed. US LISTED



Electrical Wiring Systems

P.O. Box 4822
Syracuse, NY 13221-4822
800.776.4035
www.legrand.us/PassandSeymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

