


**WEATHERPROOF - NON-GASKETED HINGED COVER ENCLOSURE**

DA



**EEMAC/NEMA Enclosure Type 3R**

**Model #MDBR - HHB**


- \* Suitable For Indoor/Outdoor Use
- \* Steel Construction - ANSI 61 Grey
- \* Cover is Hinged on Left Side With Slip-On Style Hinge
- \* Padlockable Draw Latch on Right Side
- \* Provision in Cover For Optional Key Locking T-Handle
- \* Punch Raised Rear Mounting Dimples
- \* Flat White Backpan Mounted on Panel Studs
- \* External Mounting Ear Kit Supplied Loose Inside
- \* Knockouts Supplied Only on Bottom up to 12" Enclosure



Model #	Box Size (") H x W x D	Backpan Size (") H x W	Locking Latch	Manufacturer Code	Trade Price \$
* MDBR 6-6-4 HHB	6 x 6 x 4	4.25 x 4.25	1	664-TC3R	69.20
* MDBR 8-8-6 HHB	8 x 8 x 6	6.25 x 6.25	1	886-TC3R	75.30
* MDBR 10-8-6 HHB	10 x 8 x 6	8.25 x 6.25	1	8106-TC3R	78.50
* MDBR 12-10-6 HHB	12 x 10 x 6	10.25 x 8.25	1	10126-TC3R	89.55
* MDBR 12-12-6 HHB	12 x 12 x 6	10.25 x 10.25	1	12126-TC3R	99.55
* MDBR 16-16-6 HHB	16 x 16 x 6	13 x 13	2	16166-TC3R	153.93

**WEATHERPROOF - GASKETED HINGED COVER ENCLOSURE**

DA



**EEMAC/NEMA Enclosure Type 3R**

**Model #MDBRG HHB**

- \* Suitable For Indoor/Outdoor Use
- \* Gasket Material Inside Door
- \* Steel Construction - ANSI 61 Grey
- \* Cover is Hinged on Left Side With Galvanized Piano Hinge
- \* Padlockable Draw Latch on Right Side
- \* Flat White Backpan Mounted on Panel Studs
- \* External Mounting Ears on Top And Bottom of Box
- \* No Knockouts in Enclosure



Model #	Box Size (") H x W x D	Backpan Size (") H x W	Locking Latch	Manufacturer Code	Trade Price \$
* MDBRG 6-6-4 HHB	6 x 6 x 4	4.75 x 4.75	1	664-HC3	73.80
* MDBRG 8-6-4 HHB	8 x 6 x 4	6.75 x 4.75	1	864-HC3	75.95
* MDBRG 8-8-4 HHB	8 x 8 x 4	6.75 x 6.75	1	884-HC3	77.90
* MDBRG 8-10-4 HHB	8 x 10 x 4	6.75 x 8.75	1	1084-HC3	81.00
* MDBRG 10-8-4 HHB	10 x 8 x 4	8.75 x 6.75	1	8104-HC3	81.00
* MDBRG 10-10-4 HHB	10 x 10 x 4	8.75 x 8.75	1	10104-HC3	111.90
* MDBRG 12-12-4 HHB	12 x 12 x 4	10.75 x 10.75	1	12124-HC3	121.80
* MDBRG 10-10-6 HHB	10 x 10 x 6	8.75 x 8.75	1	10106-HC3	119.25
* MDBRG 12-12-6 HHB	12 x 12 x 6	10.75 x 10.75	1	12126-HC3	122.95
* MDBRG 12-12-8 HHB	12 x 12 x 8	10.75 x 10.75	1	12128-HC3	129.75

Note: Backpan Sizes Are Approximate

**DANDY**

**A.C. DANDY PRODUCTS LTD.**



**Page #11**

Toll Free - 1-800-642-2952

R1 08-05