

WALL PLATES & LOW VOLTAGE BRACKETS

DECORATOR WALL PLATES




TP13-WH



TP26-WH



TP262-WH



TP263-WH



TP264-WH

PART NO.	DESCRIPTION
TP13-XX (WP1194-XX)	1-Gang Blank Wall Plate
TP26-XX (WP1205-XX)	1-Gang Decorator Wall Plate
TP262-XX (WP1207-XX)	2-Gang Decorator Wall Plate
TP263-XX (WP1208-XX)	3-Gang Decorator Wall Plate
TP264-XX	4-Gang Decorator Wall Plate

COLORS:

BK, BR, IV, LA, WH

DIMENSIONS:

1-GANG: 2.9375" x 4.6875"

2-GANG: 4.75" x 4.6875"

JUMBO DECORATOR Wall Plates

PART NO.	DESCRIPTION
TPJ13-XX	Jumbo 1-Gang Blank Wall Plate
TPJ26-XX	Jumbo 1-Gang Wall Plate
TPJ262-XX	Jumbo 2-Gang Wall Plate
TPJ263-XX	Jumbo 3-Gang Wall Plate

COLORS:

BK, BR, IV, LA, WH

DIMENSIONS:

1-GANG: 3.3125" X 5.0625", 2-GANG: 5.125" X 5.0625", 3-GANG: 6.9375" X 5.0625"

LOW VOLTAGE BRACKETS



AC1009-01



AC1009-02



AC1009-11



AC1010-01



AC1010-02



AC1010-03

PART NO.	DESCRIPTION
AC1009-01	1-Gang, LV Bracket w/Nail, New Construction
AC1009-02	2-Gang, LV Bracket, Face Mount, New
AC1009-11	1-Gang, LV Bracket, Face Mount, New
AC1010-01	1-Gang, LV Bracket, Retrofit
AC1010-02	2-Gang, LV Bracket, Retrofit
AC1010-03	3-Gang, LV Bracket, Retrofit

CRAFTED WITH DURABLE HEAVY-DUTY PLASTIC, ON-Q LV BRACKETS FEATURE AN OPEN BACK AND AN INTEGRATED CABLE MANAGEMENT SYSTEM FOR CLEAN CONNECTIONS AND EASY INSTALLATION

COLOR OPTIONS




STUDIO WALL PLATES


STUDIO WALL PLATES One, Two, Three & Four-Gang




WP5001-XX



WP5003-XX



WP5002-XX



WP5004-XX

PART NO.	DESCRIPTION
WP5001-XX	1-Gang Studio Wall Plate
WP5002-XX	2-Gang Studio Wall Plate
WP5003-XX	3-Gang Studio Wall Plate
WP5004-XX	4-Gang Studio Wall Plate
<p>... SCREWLESS STUDIO WALL PLATES ARE COMPATIBLE WITH ANY DECORATOR-STYLE STRAP, OUTLET OR SWITCH</p>	



COLOR OPTIONS



Gloss Black (GB)



Cement (CM)



Titanium (TI)



Khaki (KK)



Light Almond (LA)



White (WH)



Bordeaux (BD)



Cameo Pink (CP)



Spanish Red (SP)



Sand (SD)



Citrus (CR)



Taupe (TP)



Aloe (AE)



Moss (MS)



Cozumel (CZ)



Cyan (CY)



Nirvana (NV)

PRE-CONFIGURED DECORATOR STRAPS

DECORATOR STRAPS



WP3411-WH



WP3412-WH



WP3413-WH



WP3414-WH



WP3416-WH



WP3410-WH

PART NO.	DESCRIPTION
WP3411-XX	1-Port Decorator Outlet Strap Colors: BK, BR, IV, LA, WH
WP3412-XX (KS226-XX)	2-Port Decorator Outlet Strap Colors: BK, BR, IV, LA, WH
WP3413-XX (KS326-XX)	3-Port Decorator Outlet Strap Colors: BK, BR, IV, LA, WH
WP3414-XX (KS426-XX)	4-Port Decorator Outlet Strap Colors: BK, BR, IV, LA, WH
WP3416-XX	6-Port Decorator Outlet Strap Colors: BK, BR, IV, LA, WH
WP3410-XX	Blank Decorator Outlet Strap Colors: BK, BR, IV, LA, WH

PRE-CONFIGURED Wall Plates



WP3210-WH



WP3211-WH



WP3220-WH



WP3422-WH



WP1000-WH



CO1000-WH

PART NO.	DESCRIPTION
WP3210-XX	1-Port Strap, 1RJ45 Colors: BK, LA, WH
WP3211-XX	2-Port Strap Phone/TV Colors: BK, LA, WH
WP3220-XX	2-Port Strap Phone/Data Colors: BK, LA, WH
WP3422-XX	4-Port Strap Phone/Data, TV/AUX WITH THIS PRE-CONFIGURED 4-PORT STRAP YOU CAN OFFER PHONE, DATA, TV AND AN AUXILIARY LINE IN ONE DECORATOR OPENING. PERFECT FOR HOME OFFICES, MDU AND ENTERTAINMENT CENTERS. PRE-LABELLED FOR EASY ORGANIZATION. Colors: BK, LA, WH
WP1000-WH	PDP Phone/Data/Power Standard Strap (3 P w/Data) Colors: IV, LA, WH
CO1000-WH	Phone/Data Module

COLOR OPTIONS



KEYSTONE INSERTS

TELEPHONE AND DATA Keystone Inserts



WP3475-WH*



WP3476-WH



WP346A-WH



WP3450-WH*



WP3460-WH




WP3458-WH



WP3451-WH



WP3425-WH



WP3550-WH



WP3560-WH

* Available in white, light almond, and blue in packs of 50

PART NO.	DESCRIPTION
WP3475-XX	Cat 5e Quick Connect RJ45 Keystone Connector Colors: BE, BK, BR, GY, GN, IV, LA, OR, RE, WH, YE
	✦ CAN BE USED WITH THE LABOR SAVING PUNCH & GO TOOL.
WP3476-XX	Cat 6 Quick Connect RJ45 Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH
WP346A-XX	Cat 6a Quick Connect RJ45 Keystone Insert Colors: BE, BK, BR, GY, GN, IV, LA, OR, RE, WH, YE
WP3450-XX [KS58AB-XX]	Cat 5e RJ45 Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH
WP3460-XX [KS68AB-XX]	Cat 6 RJ45 Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH
WP3458-XX	Cat 5e Keyed RJ45 Keystone Connector Colors: BK, BR, IV, LA, WH
WP3451-XX [KS888-XX]	Cat 5e RJ45 Keystone Coupler Colors: BK, WH
WP3425-XX [KS6U-XX]	RJ25 6P6C Keystone Connector Colors: BK, BR, IV, LA, WH
WP3550-XX	Snap & Go Cat 5e Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH
WP3560-XX	Snap & Go Cat 6 Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH


VIDEO INSERTS




WP3479-WH*



WP3480-WH



WP3481-WH*



WP3482-WH



WP1234-WH



WP3455-WH



KSBNC-WH



KSSV-WH

*Available in packs of 50.

PART NO.	DESCRIPTION
WP3479-XX	Non-Recessed Coax Keystone F-Connector (1 GHz) 50 Count Bulk Pack in WH or LA (WP3479-XX-50)
WP3480-XX	Recessed Gold F-Connector (3GHz)
WP3481-XX [KSFF-XX]	Recessed Nickle F-Connector (3GHz) 50 Count Bulk Pack in WH (WP3481-WH-50)
WP3482-XX [KSFFST-XX]	Recessed Self-Terminating Keystone F-Connector (1 GHz)
WP1234-XX	HDMI Keystone Insert/Coupler
WP3455-XX [KSBL10-XX]	Blank Keystone Insert Colors: BK, BR, IV, LA, WH
KSBNC-XX	Keystone BNC-to-BNC Connector
KSSV-XX	Keystone S-Video-to-110 Termination Colors: IV, LA, WH

COLOR OPTIONS



KEYSTONE INSERTS

RCA-TO-F INSERTS



WP3461-WH



WP3462-WH



WP3463-WH



WP3464-WH



WP3465-WH



WP3466-WH

PART NO.	DESCRIPTION
WP3461-XX	White Keystone RCA-to-F Connector
WP3462-XX (KSRCAF-XX)	Red Keystone RCA-to-F Connector
WP3463-XX	Green Keystone RCA-to-F Connector
WP3464-XX	Blue Keystone RCA-to-F Connector
WP3465-XX	Yellow Keystone RCA-to-F Connector
WP3466-XX	Purple Keystone RCA-to-F Connector

COLORS:

BK, BR, IV, LA, WH

FIBER OPTIC INSERTS



KSSC-WH



KSST-WH

PART NO.	DESCRIPTION
KSSC-XX	Keystone SC Multimode, Phosphor Bronze Sleeve
KSST-XX	Keystone ST Multimode, Phosphor Bronze Sleeve

Colors: IV, LA, WH

MULTIMEDIA INSERTS



KSRCAY-WH



KSRCAR-WH



KSRCAB-WH



WP3457-WH



WP3456-WH

PART NO.	DESCRIPTION
KSRCAY-XX	Keystone RCA-to-RCA (Yellow Insulator) Colors: IV, LA, WH
KSRCAR-XX	Keystone RCA-to-RCA (Red Insulator) Colors: IV, LA, WH
KSRCAB-XX	Keystone RCA-to-RCA (Black Insulator) Colors: IV, LA, WH
WP3457-XX (KS2BP-XX)	Audio Keystone Binding Post - Pair Colors: BK, BR, IV, LA, WH
WP3456-XX	Speaker Pair Insert Colors: BK, BR, IV, LA, WH

COLOR OPTIONS



COMMUNICATION DEVICES

PRE-MOLDED WALLPLATES



TPTE1-WH



TPTE2-WH



26TE14-WH



26TE16-WH



WMTE14-WH



SMTE14-WH



TPCATV-WH



TPCATV2-WH



26CATV-WH



TPTELV-WH



26TELV-WH



WP3409-XX



WP3501-WH



WP3502-WH



WP3467-WH



WP2001-WH-10



WP2002-WH

PART NO.	DESCRIPTION
TPTE1-XX	2-Line Telephone Jack Wall Plate (4 Conductor Configuration) Colors: BK, BR, IV, LA, WH, GY
TPTE2-XX	Dual 2-Line Telephone Jack Wall Plate (4 Conductor Configuration) Colors: BK, BR, IV, LA, WH
26TE14-XX	Decorator 2-Line Telephone Jack (4 Conductor Configuration) Colors: IV, LA, WH
26TE16-XX	Decorator 3-Line Telephone Jack (6 Conductor Configuration) Colors: IV, WH
WMTE14-XX	2-Line Wall Mount Telephone Jack for Hanging Phones (4 Conductor Configuration) Colors: IV, LA, WH
SMTE14-XX	Surface Mount Modular 2-Line Telephone Jack (4 Conductor Configuration) Colors: IV
TPCATV-XX	1 GHz Coaxial Connector & Wall Plate Colors: IV, LA, WH, BR, BK
TPCATV2-XX	Dual 1GHz Coaxial Connector Wall Plate Colors: IV, LA, WH, BR, BK
26CATV-XX	Decorator 1 GHz Coaxial Connector Colors: IV, LA, WH
TPTELV-XX	1 GHz Coaxial Connector & 2-Line Phone Jack Wall Plate Colors: IV, LA, WH, BR, BK
26TELV-XX	1 GHz Coaxial Connector & 2-Line Phone Jack with One-Piece Molded Decorator Plate Colors: IV, LA, WH
WP3409-XX	Single Gang Surface Mount Box Colors: WH
WP3501-WH	Surface Mount Box 1-Port Colors: WH
WP3502-WH	Surface Mount Box 2-Port Colors: WH
WP3467-XX	Keystone Wall Phone Plate Colors: WH, SS (Stainless Steel)
WP2001-WH-10	Pre-Configured 1-Gang Gold F-Connector (10 Pack in WH)
WP2002-WH	1-Gang 6P6C RJ25 Terminating Wall Phone Plate Colors: WH

HOME THEATER

HOME THEATER Straps and Wallplates



F9004-WH



F9005-WH



F9006-WH



F9008-WH-V1



WP9009-WH-V1



WP1010-WH



WP1014-WH



WP9001-WH



WP9002-WH

PART NO.	DESCRIPTION
F9004-XX	5.1 Home Theater Strap TOP SELLER! Colors: BK, BR, IV, LA, WH
F9005-XX	2 Speaker Connection Strap Colors: BK, BR, IV, LA, WH
F9006-XX	Single Speaker Connection Strap Colors: BK, BR, IV, LA, WH
F9008-XX-V1	5.1 Home Theater Strap with Wall Plate Colors: DM, LA, WH
WP9009-XX-V1	7.1 Home Theater Strap with Wall Plate Colors: BK, BR, IV, LA, WH
WP1010-XX	Component Video/Digital Audio Balun Colors: BK, LA, WH CONVERTS 5.1 DIGITAL AUDIO AND COMPOSITE VIDEO TO CAT 5/CAT 6 CABLE (TWO STRAPS REQUIRED FOR INSTALLATION)
WP1014-WH	Cable Access Strap TOP SELLER!
WP9001-XX	Single Gang Bullnose Wall Plate Colors: BK, WH
WP9002-XX	Double Gang Bullnose Wall Plate Colors: BK, WH

THE BULLNOSE WALL PLATE is a unique cable management solution. Its hinged design provides four distinct configurations for flexible routing of low voltage cables inside the wall—just turn and snap the scoop for your preferred setup. (Patent Pending)

