

Aluminum Rack Panels *PBPA Series*

Install in unused rack space to improve both cooling efficiency and system esthetics.



Features

- Constructed of 6063-T6 Aluminum.
- Designed to fit standard 19" rails.
- Finished in smooth powder paint or unfinished.

Gallery



Accessories

Mounting Hardware

Part No.	Part No.	Part No.	Part No.	Part No.	Mount Dimens Rack Units H
Black	Gray/Beige	ASA 61 Gray	Light Gray	Unfinished	
PBPA 19001BK2	PBPA 19001CG2	PBPA 19001GY2	PBPA 19001LG2	PBPA 19001UNF	1U
PBPA 19003BK2	PBPA 19003CG2	PBPA 19003GY2	PBPA 19003LG2	PBPA 19003UNF	2U
PBPA 19005BK2	PBPA 19005CG2	PBPA 19005GY2	PBPA 19005LG2	PBPA 19005UNF	3U
PBPA 19007BK2	PBPA 19007CG2	PBPA 19007GY2	PBPA 19007LG2	PBPA 19007UNF	4U
PBPA 19008BK2	PBPA 19008CG2	PBPA 19008GY2	PBPA 19008LG2	PBPA 19008UNF	5U
PBPA 19010BK2	PBPA 19010CG2	PBPA 19010GY2	PBPA 19010LG2	PBPA 19010UNF	6U
PBPA 19012BK2	PBPA 19012CG2	PBPA 19012GY2	PBPA 19012LG2	PBPA 19012UNF	7U
PBPA 19014BK2	PBPA 19014CG2	PBPA 19014GY2	PBPA 19014LG2	PBPA 19014UNF	8U
PBPA 19015BK2	PBPA 19015CG2	PBPA 19015GY2	PBPA 19015LG2	PBPA 19015UNF	9U
PBPA 19017BK2	PBPA 19017CG2	PBPA 19017GY2	PBPA 19017LG2	PBPA 19017UNF	10U
PBPA 19019BK2	PBPA 19019CG2	PBPA 19019GY2	PBPA 19019LG2	PBPA 19019UNF	11U
PBPA 19021BK2	PBPA 19021CG2	PBPA 19021GY2	PBPA 19021LG2	PBPA 19021UNF	12U
PBPA 19022BK2	PBPA 19022CG2	PBPA 19022GY2	PBPA 19022LG2	PBPA 19022UNF	13U
PBPA 19024BK2	PBPA 19024CG2	PBPA 19024GY2	PBPA 19024LG2	PBPA 19024UNF	14U
PBPA 19026BK2	PBPA 19026CG2	PBPA 19026GY2	PBPA 19026LG2	PBPA 19026UNF	15U
PBPA 19028BK2	PBPA 19028CG2	PBPA 19028GY2	PBPA 19028LG2	PBPA 19028UNF	16U
PBPA 19029BK2	PBPA 19029CG2	PBPA 19029GY2	PBPA 19029LG2	PBPA 19029UNF	17U
PBPA 19031BK2	PBPA 19031CG2	PBPA 19031GY2	PBPA 19031LG2	PBPA 19031UNF	18U

*Note: "CG2" (Beige color) is being phased out from stock - replaced with "LG2" a light gray (RAL7035)

