

**Pendant Adapter**

Supports cord mounted fixtures up to 10 lbs. and stem or chain mounted fixtures to 25 lbs. Also compatible with Radius track. 6 amps.

**7599** Matte White  
**7599BK** Matte Black

**Convenience Outlet**

Provides auxiliary source for plug-in equipment. Capacity 6 amps. Also compatible with Radius track. Not UL listed.

**6085** Matte White

**Attachment Fitting**

Supports cord mounted fixtures up to 10 lbs. and stem or chain mounted fixtures to 25 lbs. Chain not included. 6 amps.

**7589** Matte White  
**7589BK** Matte Black

**Basic Monopoint**

Ultra shallow Monopoint mounts track fixtures to 3 1/2" or 4" octagon outlet box (1/4" deep).

4 1/2" dia. canopy  
**6190WH** Matte White  
**6190BK** Matte Black  
**6190NAL** Aluminum  
(Use 90°C Min. supply wire.)

**Rectangular Monopoint**

Ultra shallow Monopoint mounts track fixtures to 3 1/2" or 4" octagon outlet box (1/4" deep).

**6170WH** Matte White  
**6170BK** Matte Black  
**6170AL** Aluminum  
(Use 90°C Min. supply wire.)

**Cord and Plug**


For Basic 1-circuit track only. Includes 15-foot, 2-conductor cord and plug set with in-line switch. Capacity 7 amps at 120V. Not UL Listed.

**6062WH** Matte White Basic Only  
**6062BK** Matte Black Basic Only

**Monopoint Pin-Up**

Wall mounts one Lytespot®. 15' cord and plug, built-in switch. 4 1/2" diameter.

**6194WH** Matte White

**Multipoint**

Surface mounts of up to 3 average sized Lytespots®, depending on the fixture size, over any standard outlet box. Track length 11 11/16", width 4 1/2", depth 9/16". Note: Not compatible with Lyteflood 39 and Lyteflood 40.

**7619WH** Matte White

**Weighted Base**


Powers one Lytespot®. Includes 8' cord and plug, built-in switch. Note: Not compatible with Power Jacks, Lyteflood 39 or Lyteflood L40. Do not install less than 5 feet above the floor.

**6197BK** Matte Black

**Extension Wands**

Extends Lytespots® below track. Stem dia. 1/2". Can be connected together -8' max. Can be used with all fixtures listed with this symbol. Also compatible with Radius Track. May not be field cut.

**48"**  
**6076WH** Matte White  
**6076BK** Matte Black  
**36"**  
**6075WH** Matte White  
**6075BK** Matte Black  
**18"**  
**6074WH** Matte White  
**6074BK** Matte Black

**Clamp-On Monopoint**

Can be clamped on pipe up to 2" diameter, comes with 8' cord and plug. Can be used with all fixtures listed with this symbol.

**6196WH** Matte White  
**6196BK** Matte Black