



F32T8 TL735 ALTO

Product family description
Extra low mercury

Features/Benefits

- Extended Life
- Reduce maintenance costs by extending the relamping cycle
- Warranty period: 30 months
- Outstanding lumen performance
- 95% lumen maintenance and reduced lamp-end blackening
- Better for the environment
- Only 1.7mg of mercury with ALTO II™ Technology
- Reduced impact on the environment without sacrificing performance

Applications

- Ideal for applications requiring maximum maintained light output.

Notes


- Rated average life under specified test conditions with lamps turned off and restarted no more frequently than once every 3 operating hours. Lamp life is appreciably longer if lamps are started less frequently. (202)
- Average life under engineering data with lamps turned off and restarted once every 12 operating hours.(241)
- Approximate Initial Lumens. The lamp lumen output is based upon lamp performance after 100 hours of operating life, when the output is measured during operation on a reference ballast under standard laboratory conditions. (203)
- For expected lamp lumen output, commercial ballast manufacturers can advise the appropriate Ballast Factor for each of their ballasts when they are informed of the designated lamp. The Ballast Factor is a multiplier applied to the designated lamp lumen output. (204)
- Design Lumens are the approximate lamp lumen output at 40% of the lamp's Rated Average Life. This output is based upon measurements obtained during lamp operation on a reference ballast under standard laboratory conditions. (208)

Product data	
Product Number	272492
Full product name	F32T8 TL735 ALTO
Ordering Code	F32T8/TL735/ALTO

Product data	
Pack type	1 Lamp
Pieces per Sku	1
Skus/Case	25
Pack UPC	046677272494
EAN2US	
Case Bar Code	50046677272499
Successor Product number	
Base	Medium Bi- Pin [Medium Bi- Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Packing Type	1LP [1 Lamp]
Packing Configuration	25
Type	F32T8
Feature	ALTO®
Ordering Code	F32T8/TL735/ALTO
Pack UPC	046677272494
Case Bar Code	50046677272499
Energy Saving	Energy Saving
Rated Avg Life [12- Hr Prog St]	36000 hr
Rated Avg Life [12- Hr Inst St]	30000 hr
Rated Avg Life [3- Hr Prog St]	30000 hr
Rated Avg Life [3- Hr Inst St]	24000 hr
Watts	32W
Mercury (Hg) Content	3.5 mg
Color Code	TL735 [CCT of 3500K]
Color Rendering Index	78 Ra8
Color Designation	TL735
Color Temperature	3500 K
Initial Lumens	2800 Lm
Design Mean Lumens	2660 Lm
Nominal Length [inch]	48
Product Number	272492




F-T8- Unv Med Bipin/GB



Base Medium Bi- Pin



Energy Saving Energy Saving



F-T8- Unv Med Bipin

