

**PHILIPS**

LED

3-Way A21



# Versatile LED bulb provides three light level options

Philips 3-Way LED A21 bulb offers three levels of comfortable, soft white light in a single energy-efficient light bulb. When used with a standard 3-way luminaire this bulb delivers light equivalent to either a 40W, 60W or 100W incandescent bulb.

## LED benefits with the ambiance of incandescent    Easy to experience

- 40W/60W/100W Energy Star® equivalent lumens
- Available in 2700K
- 25,000 hour life<sup>1</sup>
- All-around light
- Life not affected by frequent switching cycles
- Enjoy the energy-savings of LEDs without sacrificing light quality
- 3-year limited warranty<sup>2</sup>
- Smooth, even glow

# Philips 3-way LED A21 Lamps

## Ordering, Electrical and Technical Data (Subject to change without notice)

Product Number	Model Number	Order Code	LED Watts	Bulb	Dim?	Rated Avg. Life (Hrs.) <sup>1</sup>	Nominal Lumens	CRI	CCT (K)	MOL (in.)	Dia (in.)
<b>Standard Incandescent A19 40W/60W/100W Energy Star® Equivalent</b>											
45336-5	9290011219	20A21/END/2700 3W DIM 120V	5/9/20	A21	N	25,000	470/840/1620	>80	2700	4.95	2.61

## Shipping Data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKU per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W x D x H) (In.)
45336-5	45336-7	45336-2	6	4.13	0.163	1224	204	6	2.7 x 2.7 x 5.1	8.5 x 5.8 x 5.7	47.2 x 39.4 x 39.7

### WARNINGS AND CAUTIONS

- Suitable for use in damp locations.
- Do not use in outdoor fixtures.
- Not for use in totally enclosed luminaires.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.

**CAUTION:** Risk of electric shock— do not use where directly exposed to water.

**NOTES:** This device complies with Part 15 of the FCC rule. Operation is subject to the following two conditions: (1) device may not cause harmful interference, and (2) This device must accept any interference received, including, interference that may cause undesired operation. This Class B digital apparatus complies with Canadian ICES-003.

1. Rated average life based on engineering testing and probability analysis.
2. For details, please visit [www.philips.com/warranties](http://www.philips.com/warranties).

© 2014 Koninklijke Philips N.V. All rights reserved.  
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting, North America Corporation  
200 Franklin Square Drive, Somerset, NJ 08873  
Tel. 855-486-2216

Imported by: Philips Lighting,  
A division of Philips Electronics Ltd.  
281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
Tel. 800-668-9008