



# PL-T Triple 4-Pin Base

PL-T ALTO 26W/835 /4P A

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

## Product data

### • General Characteristics

Base	GX24q-3
Base Information	4P
Life to 50% fail	10000 hr
Nonpreh EL,3h	
LSF HF Preheat	99 %
2000h Rated,3h	
LSF HF Preheat	98 %
4000h Rated,3h	
LSF HF Preheat	97 %
6000h Rated,3h	
LSF HF Preheat	90 %
8000h Rated,3h	
LSF HF Preheat	60 %
12000h Rated,3h	

### • Light Technical Characteristics

Color Code	835 [CCT of 3500K]
Color Rendering Index	82 Ra8
Color Designation	White
Color Temperature	3500 K
Luminous Flux EL	1750 Lm
25°C, Rated	
Luminous Flux EL	1750 Lm
25°C, Nominal	
Lum Efficacy Rated	64.8 Lm/W
HF 25°C	
LLMF HF 2000h	92 %
Rated	
LLMF HF 4000h	88 %
Rated	
LLMF HF 6000h	85 %
Rated	
LLMF HF 8000h	84 %
Rated	

LLMF HF 12000h	81 %
Rated	
Design Temperature	28 C
Chromaticity Coordinate X	412 -
Chromaticity Coordinate Y	402 -

### • Electrical Characteristics

Watts	26 W
Lamp Wattage EL	27.0 W
25°C, Rated	
Lamp Wattage EL	27 W
25°C, Nominal	
Lamp Voltage EL	106 V
25°C	
Lamp Current EL	0.335 A
25°C	
Dimmable	Yes

### • Environmental Characteristics

Energy Efficiency Label (EEL)	B
Mercury (Hg) Content	1.4 mg

### • Measuring Conditions

Calibration Current	0.320 A
---------------------	---------

### • Product Dimensions

Base Face to Base Face A	86.7 (max) mm
Insertion Length B	111.0 (max) mm

**PHILIPS**

# PL-T Triple 4-Pin Base


Overall Length C 126.7 (max) mm  
 Diameter D 41 (max) mm

• **Product Data**

Product number 458265  
 Full product name PL-T ALTO 26W/835 /4P A  
 Short product name PL-T 26W/835/A/4P/ALTO



Pieces per Sku 1  
 eop\_pck\_cfg 10  
 Skus/Case 10  
 Bar code on pack 46677268244  
 Bar code on case 50046677458268  
 Logistics code(s) 927910983550  
 tpd\_ilcos\_cd FSM-26/35/1B-E-GX24q=3  
 eop\_net\_weight\_pp 64.000 gr

## Dimensional drawing





### PL-T ALTO 26W/835 /4P A

Product	A (Max)	B (Max)	C (Max)	D (Max)
PL-T ALTO 26W/835/4P A	86.7	111.0	126.7	41



## Photometric data



© 2015 Koninklijke Philips N.V. (Royal Philips)  
 All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2015, July 27  
 data subject to change