

## SOCKET TAPPING SCREWS VIS TARAUDEUSES CREUSE

**208**  
Pan  
Head



**209**  
Flat  
Head



**210**  
Truss  
Head



- Sheet Metal Screws, Self-Tapping, Hardened.

Loxon® Square Socket Drive

Specify Papco® Pan, Flat or Truss Socket Head Tapping Screws where a positive driver engagement, or where high-speed assembly of sheet metal parts, is required. They are used in body work, moldings, trim, sheet metal work and many other applications.

### ORDER BY STOCK NUMBER

Standard Package: 100 Pieces

Pan Head Stock No.	Flat Head Stock No.	Truss Head Stock No.	Screw Dia.	Screw Length	Decimal Equiv. of Dia.	Drill Hole	Pan Head Stock No.	Flat Head Stock No.	Truss Head Stock No.	Screw Dia.	Screw Length	Decimal Equiv. of Dia.	Drill Hole
208-039				1/4			208-187				3/8		
208-041	209-041			3/8			208-189	209-189	210-189		1/2		
208-043	209-043		4	1/2	.112	5/64	208-190	209-190	210-190		5/8		
208-045	209-045			3/4			208-191	209-191	210-191	10	3/4	.191	9/64
208-047	209-047			1			208-193	209-193	210-193		1		
208-083				1/4			208-195	209-195	210-195		1-1/4		
208-085	209-085	210-085		3/8			208-197	209-197			1-1/2		
208-087	209-087	210-087		1/2			208-200	209-200			2		
208-088	209-088	210-088	6	5/8	.138	3/32	208-246	209-246			1/2		
208-089	209-089	210-089		3/4			208-248	209-248			3/4		
208-091	209-091	210-091		1			208-250	209-250		12	1	.218	5/32
208-093	209-093			1-1/4			208-252	209-252			1-1/4		
208-095	209-095			1-1/2			208-254	209-254			1-1/2		
208-135		210-135		3/8			208-257				2		
208-137	209-137	210-137		1/2			208-277	209-277			5/8		
208-138	209-138	210-138		5/8			208-278	209-278			3/4		
208-139	209-139	210-139	8	3/4	.165	1/8	208-280	209-280		14	1	.251	3/16
208-141	209-141	210-141		1			208-282	209-282			1-1/4		
208-143	209-143	210-143		1-1/4			208-284	209-284			1-1/2		
208-145	209-145	210-145		1-1/2			208-287	209-287			2		
208-148	209-148			2									

## HEX HEAD TAPPING SCREWS VIS TARAUDEUSES TÊTE HEX

**213**  
Hex Head



- Self-Tapping and Hardened.

Oversize Hexagon Washer Heads to fit Automotive Cap Screw Wrenches.

### ORDER BY STOCK NUMBER

Standard Package: 100 Pieces

Stock No.	Screw Dia.	Screw Length	Decimal Equiv. of Dia.	Across Flats	Drill Hole	Stock No.	Screw Dia.	Screw Length	Decimal Equiv. of Dia.	Across Flats	Drill Hole
213-085	6	3/8	.138	1/4	3/32	213-250	12	1	.218	5/16	5/32
213-137		1/2				213-276		1/2			
213-139		3/4				213-277		5/8			
213-141	8	1	.165	1/4	1/8	213-278	14	3/4	.251	7/16	3/16
213-143		1-1/4				213-280		1			
213-145		1-1/2				213-282		1-1/4			
213-187		3/8				213-284		1-1/2			
213-189		1/2				213-442		3/4			
213-190	10	5/8	.191	5/16	9/64	213-444	5/16	1	.312	1/2	9/32
213-191		3/4				213-446		1-1/4			
213-193		1				213-448		1-1/2			
213-246		1/2				213-489		1			
213-248	12	3/4	.218	5/16	5/32	213-493	3/8	1-1/2	.375	9/16	11/32

## 'SUPER-SERVICE' ASSORTMENT

### No. 020-808

Contains 650 Hexagon Head Tapping Screws and Fender Washers. Large size, rigid metal box with high-strength plastic compartments. For more details see page 10. Size: 12" W x 18" L x 3" D.



020-808