



# 18.8 Stainless Steel HEX HEAD CAP SCREWS

UNC - Unified National Coarse Thread

**Series  
5000**



SIZE No	DIAMETER X LENGTH	PKG QTY	CASE QTY
---------	-------------------	---------	----------

### 1/4" Diameter

- 303	1/4-20 x 3/8	100	2000
- 305	1/4-20 x 1/2	100	3000
- 306	1/4-20 x 5/8	100	2000
- 307	1/4-20 x 3/4	100	2000
- 308	1/4-20 x 7/8	100	2000
- 309	1/4-20 x 1	100	2000
- 311	1/4-20 x 1-1/4	100	1600
- 313	1/4-20 x 1-1/2	100	1600
- 315	1/4-20 x 1-3/4	100	1200
- 316	1/4-20 x 2	100	1200
- 317	1/4-20 x 2-1/4	50	800
- 318	1/4-20 x 2-1/2	50	600
- 319	1/4-20 x 2-3/4	50	600
- 320	1/4-20 x 3	25	400
- 321	1/4-20 x 3-1/4	25	400
- 322	1/4-20 x 3-1/2	25	400
- 324	1/4-20 x 4	25	400
- 325	1/4-20 x 4-1/2	10	160
- 326	1/4-20 x 5	10	80
- 327	1/4-20 x 5-1/2	10	80
- 329	1/4-20 x 6	10	80

### 5/16" Diameter

- 440	5/16-18 x 1/2	100	2000
- 441	5/16-18 x 5/8	100	2000
- 442	5/16-18 x 3/4	100	1600
- 443	5/16-18 x 7/8	100	1600
- 444	5/16-18 x 1	100	1600
- 446	5/16-18 x 1-1/4	100	1200
- 448	5/16-18 x 1-1/2	100	1200
- 450	5/16-18 x 1-3/4	100	800
- 451	5/16-18 x 2	100	800
- 452	5/16-18 x 2-1/4	50	400
- 453	5/16-18 x 2-1/2	50	400

SIZE No	DIAMETER X LENGTH	PKG QTY	CASE QTY
---------	-------------------	---------	----------

### 5/16" Diameter

- 454	5/16-18 x 2-3/4	50	400
- 455	5/16-18 x 3	25	400
- 456	5/16-18 x 3-1/4	25	400
- 457	5/16-18 x 3-1/2	25	400
- 459	5/16-18 x 4	25	400
- 460	5/16-18 x 4-1/2	10	80
- 461	5/16-18 x 5	10	80
- 462	5/16-18 x 5-1/2	10	80
- 464	5/16-18 x 6	10	80

### 3/8" Diameter

- 485	3/8-16 x 1/2	100	1600
- 486	3/8-16 x 5/8	100	1600
- 487	3/8-16 x 3/4	100	1200
- 488	3/8-16 x 7/8	100	1200
- 489	3/8-16 x 1	100	1200
- 491	3/8-16 x 1-1/4	100	800
- 493	3/8-16 x 1-1/2	100	800
- 495	3/8-16 x 1-3/4	100	600
- 496	3/8-16 x 2	100	600
- 497	3/8-16 x 2-1/4	50	400
- 498	3/8-16 x 2-1/2	50	400
- 499	3/8-16 x 2-3/4	25	400
- 500	3/8-16 x 3	25	200
- 501	3/8-16 x 3-1/4	25	200
- 502	3/8X3 1/2	25	200
- 503	3/8X3 3/4	25	200
- 504	3/8X4	25	200
- 505	3/8X4 1/2	10	80
- 506	3/8X5	10	80
- 507	3/8X5 1/2	10	80
- 509	3/8X6	10	80
- 510	3/8X6 1/2	Bulk:	240
- 511	3/8X7	Bulk:	240
- 513	3/8X8	Bulk:	200

Note: Please use Series and Size No. when ordering:



Example: 1/4-20 x 1 UNC 18.8 Stainless Steel Hex Head Cap Screw  
Series - Size.  
5000 - 309

Stock Sizes are shown in **HEAVY** type.

# 18.8 Stainless Steel HEX HEAD CAP SCREWS

UNC - Unified National Coarse Thread

**Series  
5000**



SIZE No	DIAMETER X LENGTH	PKG QTY	CASE QTY
---------	-------------------	---------	----------

### 3/8" Diameter

-515	3/8X9	Bulk:	180
-517	3/8X10	Bulk:	180

### 7/16" Diameter

-532	7/16-14X3/4	25	800
-534	7/16-14X1	25	800
-536	7/16-14X1 1/4	25	600
-538	7/16-14X1 1/2	25	600
-540	7/16-14X1 3/4	25	400
-541	7/16-14X2	20	400
-542	7/16-14X2 1/4	20	400
-543	7/16-14X2 1/2	20	300
-544	7/16-14X2 3/4	10	300
-545	7/16-14X3	10	200
-547	7/16-14X3 1/2	10	200
-549	7/16-14X4	10	200
-550	7/16-14X4 1/2	10	200
-551	7/16-14X5	10	200

### 1/2" Diameter

-577	1/2-13X3/4	25	500
-578	1/2-13X7/8	25	300
-579	1/2-13X1	25	500
-581	1/2-13X1 1/4	25	400
-583	1/2-13X1 1/2	25	200
-585	1/2-13X1 3/4	25	200
-586	1/2-13X2	20	240
-587	1/2-13X2 1/4	20	240
-588	1/2-13X2 1/2	20	240
-589	1/2-13X2 3/4	20	160
-590	1/2-13X3	10	160
-591	1/2-13X3 1/4	10	80
-592	1/2-13X3 1/2	10	80
-593	1/2-13X3 3/4	10	80
-594	1/2-13X4	10	80

SIZE No	DIAMETER X LENGTH	PKG QTY	CASE QTY
---------	-------------------	---------	----------

### 1/2" Diameter

-595	1/2-13X4 1/2	10	80
-596	1/2-13X5	10	80
-597	1/2-13X5 1/2	10	80
-599	1/2-13X6	10	80
-600	1/2-13X6 1/2	10	40
-601	1/2-13X7	10	40
-602	1/2-13X7 1/2	10	40
-603	1/2-13X8	10	40
-604	1/2-13X8 1/2	Bulk:	120
-605	1/2-13X9	Bulk:	120
-607	1/2-13X10	Bulk:	120

### 5/8" Diameter

-668	5/8-11X1	25	300
-670	5/8-11X1 1/4	25	300
-672	5/8-11X1 1/2	25	200
-674	5/8-11X1 3/4	20	160
-675	5/8-11X2	20	120
-676	5/8-11X2 1/4	20	160
-677	5/8-11X2 1/2	20	160
-678	5/8-11X2 3/4	20	120
-679	5/8-11X3	10	80
-680	5/8-11X3 1/4	10	80
-681	5/8-11X3 1/2	10	80
-682	5/8-11X3 3/4	10	80
-683	5/8-11X4	10	80
-684	5/8-11X4 1/2	10	80
-685	5/8-11X5	10	80
-686	5/8-11X5 1/2	10	80
-688	5/8-11X6	10	80
-689	5/8-11X6 1/2	Bulk:	70
-690	5/8-11X7	Bulk:	70
-692	5/8-11X8	Bulk:	60
-696	5/8-11X10	Bulk:	75

Note: Please use Series and Size No. when ordering:

Example: 7/16-14 x 2 18.8 Stainless Steel Hex Head Cap Screws



Series Size No.  
5000 -541

Stock Sizes are shown in **HEAVY** type.

# 18.8 Stainless Steel HEX HEAD CAP SCREWS

UNC - Unified National Coarse Thread

**Series  
5000**



SIZE No	DIAMETER X LENGTH	PKG QTY	CASE QTY
---------	-------------------	---------	----------

### 3/4" Diameter

-712	3/4-10X1 1/4	20	120
-714	3/4-10X1 1/2	20	120
-716	3/4-10X1 3/4	20	120
-717	3/4-10X2	20	120
-718	3/4-10X2 1/4	20	120
-719	3/4-10X2 1/2	20	120
-720	3/4-10X2 3/4	20	120
-721	3/4-10X3	10	80
-722	3/4-10X3 1/4	10	80
-723	3/4-10X3 1/2	10	60
-724	3/4-10X3 3/4	Bulk:	90
-725	3/4-10X4	10	60
-726	3/4-10X4 1/2	10	60
-727	3/4-10X5	10	60
-728	3/4-10X5 1/2	10	60
-730	3/4-10X6	10	40
-731	3/4-10X6 1/2	Bulk:	60
-732	3/4-10X7	Bulk:	60
-734	3/4-10X8	Bulk:	60
-738	3/4-10X10	Bulk:	50

### 7/8" Diameter

-759	7/8-9X1 1/2	10	60
-761	7/8-9X1 3/4	10	60
-762	7/8-9X2	10	60
-763	7/8-9X2 1/4	10	60
-764	7/8-9X2 1/2	10	60
-765	7/8-9X2 3/4	10	60
-766	7/8-9X3	10	60
-768	7/8-9X3 1/2	10	60
-770	7/8-9X4	10	60
-771	7/8-9X4 1/2	10	60
-772	7/8-9X5	10	60
-773	7/8-9X5 1/2	10	40

SIZE No	DIAMETER X LENGTH	PKG QTY	CASE QTY
---------	-------------------	---------	----------

### 7/8" Diameter

-775	7/8-9X6	10	40
-776	7/8-9X6 1/2	Bulk:	45
-777	7/8-9X7	Bulk:	45
-779	7/8-9X8	Bulk:	45
-783	7/8-9X10	Bulk:	40

### 1" Diameter

-803	1-8X2	Bulk:	90
-804	1-8X2 1/4	Bulk:	85
-805	1-8X2 1/2	Bulk:	80
-806	1-8X2 3/4	Bulk:	70
-807	1-8X3	Bulk:	65
-808	1-8X3 1/4	Bulk:	60
-809	1-8X3 1/2	Bulk:	60
-810	1-8X3 3/4	Bulk:	50
-811	1-8X4	Bulk:	40
-812	1-8X4 1/2	Bulk:	40
-813	1-8X5	Bulk:	40
-814	1-8X5 1/2	Bulk:	40
-816	1-8X6	Bulk:	30
-817	1-8X6 1/2	Bulk:	35
-818	1-8X7	Bulk:	35
-820	1-8X8	Bulk:	30
-821	1-8X8 1/2	Bulk:	30
-822	1-8X9	Bulk:	30
-824	1-8X10	Bulk:	30

Note: Please use Series and Size No. when ordering:

Example: 3/4-10 x 10 UNC 18.8 Stainless Steel Hex Head Cap Screws

Series Size No.  
5000 -738

Stock Sizes are shown in **HEAVY** type.