


# Outdoor Cords

## Landscape Cords

### Single Outlet, 2 & 3 Conductor

- GD Series + PL Series:
  - 2-conductor, polarized plug.
- GC Series :
  - 3 conductor, grounded.



ORDER NO.	PRODUCT CODE	GAUGE/ CONDUCTOR	WIRE TYPE	CORD LENGTH (M)	CORD COLOUR	PACK SIZE	SHIP CARTON MC/TRAY/DB
-----------	--------------	------------------	-----------	-----------------	-------------	-----------	------------------------

#### 2-CONDUCTOR POLARIZED


538444	GD1610MORG	16/2	SJTW	10	Orange	12	TRAY
538448	GD1615MORG	16/2	SJTW	15	Orange	10	TRAY
543252	GD1630MORG	16/2	SJTW	30	Orange	3	TRAY
543260	PL1676MWH	16/2	SJTW	7.6	White	9	TRAY
543261	PL1676MGRN	16/2	SJTW	7.6	Green	9	TRAY
543262	PL1676MCED	16/2	SJTW	7.6	Cedar	9	TRAY

#### 3-CONDUCTOR POLARIZED

542107	GC315MYEL	16/3	SJTW	15	Yellow	10	TRAY
542111	GC325MYEL	16/3	SJTW	25	Yellow	6	TRAY
550393	GC312MGRN	16/3	SJTW	12	Green	12	TRAY
550394	GC324MGRN	16/3	SJTW	24	Green	6	TRAY

## Multi-Outlet Cords

- Unlike conventional cords, this cord has outlets spaced along the cord, where multiple outlets are required.
- Allows easy placement of large tools, landscape lighting or displays.
- 3-outlets spaced every 8 feet (547727) or 3-outlets spaced every 3 feet (547728)
- Illuminated outlets indicate cord has power (547728)
- Extra durable, super flexible




ORDER NO.	PRODUCT CODE	GAUGE/ CONDUCTOR	WIRE TYPE	CORD LENGTH (M)	CORD COLOUR	PACK SIZE	SHIP CARTON MC/TRAY/DB
547727	MOUT776M	14/3	STW	7.6	Green	6	TRAY
547728	MOMT727M	14/3	STW	2.7	Black	6	TRAY

Outdoor Cords are made with specially treated, double-insulated jackets that offer the following:

- Weather-proof • Resistant to UV rays • Stay flexible when in use even in -40° cold weather.
- Powerlite™ indicator plug (in Power Indicator cords) glows when the cord has power.

## Single Outlet



ORDER NO.	PRODUCT CODE	GAUGE/ CONDUCTOR	WIRE TYPE	CORD LENGTH (M)	CORD COLOUR	PACK SIZE	SHIP CARTON MC/TRAY/DB
Single Outlet							
541504	UT403M	16/3	SJTW	3	Orange	14	TRAY
541506	UT405M	16/3	SJTW	5	Orange	21	TRAY
541522	UT410M	16/3	SJTW	10	Orange	12	TRAY
541548	UT415M	16/3	SJTW	15	Orange	10	TRAY
541564	UT430M	16/3	SJTW	30	Orange	3	TRAY
567670	UT403MBLK	16/3	SJTW	3	Black	14	TRAY
567677	UT410MBLK	16/3	SJTW	10	Black	12	TRAY
541570	UT610M	14/3	SJTW	10	Red	13	TRAY
541574	UT615M	14/3	SJTW	15	Red	8	TRAY
536778	UT630M	14/3	SJTW	30	Red	3	TRAY
541552	UT710M	12/3	SJTW	10	Yellow	10	TRAY
541553	UT715M	12/3	SJTW	15	Yellow	6	TRAY
541554	UT730M	12/3	SJTW	30	Yellow	3	TRAY

Single Outlet with Power Indicator Light							
541508	MT405M	16/3	SJTW	5	Orange	21	TRAY
541524	MT410M	16/3	SJTW	10	Orange	12	TRAY
541550	MT415M	16/3	SJTW	15	Orange	10	TRAY
541566	MT430M	16/3	SJTW	30	Orange	3	TRAY
541555	MT610M	14/3	SJTW	10	Red	13	TRAY
541556	MT615M	14/3	SJTW	15	Red	8	TRAY
541557	MT630M	14/3	SJTW	30	Red	3	TRAY
541558	MT710M	12/3	SJTW	10	Yellow	10	TRAY
541559	MT715M	12/3	SJTW	15	Yellow	6	TRAY
541560	MT730M	12/3	SJTW	30	Yellow	3	TRAY