








		For use with	Part no. Article no. when ordered separately	Price see price list	Std. pack	Notes
CSA only						
Door coupling rotary handle						
Complete including rotary drive and coupling parts An additional extension shaft is necessary with the NZM...-XT(V)D(V)(R)(-60) types. Degree of protection IP66/UL/CSA Type 4X						
Standard, black/grey						
 	Lockable in 0 position on handle. With door interlock	NZM1, N1	NZM1-XTVD 260166			Door interlock <ul style="list-style-type: none"> • Not defeated in the locked OFF and ON positions • Can be modified such that it can be defeated from the outside using a screwdriver, when it is in the unlocked ON position. • Door can be opened in OFF NZM...-XTVD(V) • External warning plate/ designation label can be clipped on
		NZM2, N2	NZM2-XTVD 260168			
		NZM3, N3	NZM3-XTVD 260170			
		NZM4, N4	NZM4-XTVD 266614			
 	Lockable on handle and switch. Can be locked in 0 position, with adequate modification also in I position. With door interlock Lockable in 0 position on circuit-breaker.	NZM1, N1	NZM1-XTVDV 260172			
		NZM2, N2	NZM2-XTVDV 260174			
		NZM3, N3	NZM3-XTVDV 260176			
		NZM4, N4	NZM4-XTVDV 266616			
Red-yellow for Emergency-Stop						
 	Lockable on handle and switch. Lockable in 0 position on handle. With door interlock Lockable in 0 position on circuit-breaker.	NZM1, N1	NZM1-XTVDVR 260178		1 off	Door interlock <ul style="list-style-type: none"> • Not defeatable in the locked OFF position. • Can be modified such that it can be defeated from the outside using a screwdriver, when it is in the unlocked ON position. • Door can be opened in OFF NZM...-XTVDVR • External warning plate/ designation label can be clipped on
		NZM2, N2	NZM2-XTVDVR 260180			
		NZM3, N3	NZM3-XTVDVR 260182			
		NZM4, N4	NZM4-XTVDVR 266618			
Extension shaft						
	Max. mounting depth: 400 mm	NZM1, N1	NZM1/2-XV4 261232		1 off	Can be cut to required length
		NZM2, N2				
		NZM3, N3	NZM3/4-XV4 261234			
		NZM4, N4				
	Max. mounting depth: 600 mm	NZM1, N1	NZM1/2-XV6 260191			
		NZM2, N2				
		NZM3, N3	NZM3/4-XV6 260193			
		NZM4, N4				

Notes

Circuit-breaker can also be installed in a lying position 90° left/right, with the handle still in the same position.