

# Fibersnakes

Fibersnake Fishtapes and Rodders are designed for use in conduit. The reinforced fiberglass core is jacketed with a plastic coating for superior flexibility and durability. Non-conductive, so it's great for conduit with existing wiring. Rust-proof brass tips and fittings.

## 3/16" FIBERSNAKE

FIBT50 50' Fibersnake  
FIBT100 100' Fibersnake  
FIBT150 150' Fibersnake  
FIBT200 200' Fibersnake  
FIBT250 250' Fibersnake  
FIBT300 300' Fibersnake

RT50 50' Replacement Rodder only  
RT100 100' Replacement Rodder only  
RT150 150' Replacement Rodder only  
RT200 200' Replacement Rodder only  
RT250 250' Replacement Rodder only  
RT300 300' Replacement Rodder only

## 1/4" FIBERSNAKE

FIBR200 200' Fibersnake  
FIBR250 250' Fibersnake  
FIBR300 300' Fibersnake  
FIBR350 350' Fibersnake  
FIBR400 400' Fibersnake  
FIBR450 450' Fibersnake  
FIBR500 500' Fibersnake  
FIBR550 550' Fibersnake  
FIBR600 600' Fibersnake

RR200 200' Replacement Rodder only  
RR250 250' Replacement Rodder only  
RR300 300' Replacement Rodder only  
RR350 350' Replacement Rodder only  
RR400 400' Replacement Rodder only  
RR450 450' Replacement Rodder only  
RR500 500' Replacement Rodder only  
RR550 550' Replacement Rodder only  
RR600 600' Replacement Rodder only

## 5/16" FIBERSNAKE

Fibersnakes and Replacement Rodders are available in 400'-1000' Fibersnakes Part # FIBL400-FIBL1000 Replacement Rodder Part # RL400-RL1000

Our 5/16" Fibersnakes are made to order. Returns due to the wrong size being ordered will **NOT** be accepted. Please order carefully.

Rodder Diameter	Recommended conduit sizes (in inches)	Maximum Length
(FIBT) 3/16"	1/2, 3/4, 1, 1 1/4	300'
(FIBR) 1/4"	1, 1 1/4, 1 1/2, 2, 2 1/2	600'
(FIBL) 5/16"	1 1/2, 2, 2 1/2, 3, 3 1/2, 4	1000'



Fibersnakes are designed to pull fish line or rope. They are not recommended for pulling wire and cable.

**Note:** We do not replace fibersnakes broken due to improper use. However, we will send a repair kit at no extra charge.

## Super Wrist Magnet

- Holds any steel parts
- Comfortable to wear all day
- Made of rugged 2 mil neoprene
- Waterproof
- Adjustable band fits virtually any wrist size



Part #WM396

## Contractor Packs

### Installer Pack


Fiberfish II Kit; 1/2"x72" Auger Piranhabit; 3/8"x72" HSS Piranhabit; 20' Fiberglass Telepole; Attachment Kit; Carry Case.

Part #CON100 Installer Kit

### Contractor Pack

Fiberfish II Kit; 1/2"x72" Auger Piranhabit; 3/8"x72" HSS Piranhabit; 20' Fiberglass Telepole; Attachment Kit; Wisp Head; Flex Fish; Steering Guide; 1" Auger Bit; Carry Case.

Part #CON200 Contractor Pack



## Attachment Kit

Contains: FishHook, Directional Tool, Magnet Head, Pull Ring, Ball Chain, and 2 replacement tips. Stored in convenient vinyl pouch.



FIB120 Fiberfish Attachment Kit (1/4" rods)  
FIB520 Universal Attachment Kit for ALL (3/16" rods) & (5/32" rods)

## Master Attachment Kit

Contains same as above plus: Wisp Head, Screw Tip, Flex-Fish



FIB140 Fiberfish Master Attachment Kit (1/4" rods)  
FIB540 Universal Master Attachment Kit for ALL (3/16" rods) & (5/32" rods)