

Medium Base Ceiling Lampholders

Medium Base
660W, 125V/AC
660W, 250V/AC

Medium Base Ceiling Lampholders

Features

- Mounts on 4" (101.6mm) outlet boxes with breakout for 3.25" (82.5mm) box mounting
- Leads are 6" (152.4mm) 221°F (105°C) insulated stranded #16, stripped 0.75" (19.0mm)
- Pull chain devices include ball chain, 3' (0.9m) of cord, connector and end bell
- Top wire versions have terminal screws backed out – ready for wiring – without removing interior
- Push wire terminals are top wired with two push-in terminals and two screw terminals for continuous wiring
- Plastic models made with high-temperature thermoset plastic to reduce breakage
- Porcelain models made with high-strength insulator porcelain; pull chain versions feature removable interiors

Plastic Ceiling Lampholders



Rating		Description	Color	Catalog No.		
W	V/AC					
660	250	Two Piece, Push Wire/Top Wire, Pull Chain Switch	W	<input type="checkbox"/> S759W-CD		
		Two Piece, 6" (152.4mm) Leads, Pull Chain Switch	W	<input type="checkbox"/> S788W		
		Two Piece, w/ 15A 125V/AC 2P 3W Outlet, Push Wire/Top Wire, Pull Chain Switch	W	<input type="checkbox"/> S865W		
		One Piece, 4 Top Wire Screws, Keyless Switch	W	<input type="checkbox"/> S1174W		•
		One Piece, 6" (152.4mm) Leads, Keyless Switch	W	<input type="checkbox"/> S1174-6W*		•
		Two Piece, Push Wire/Top Wire, Keyless Switch	W	<input type="checkbox"/> S768W		
		Two Piece, 6" (152.4mm) Leads, Keyless Switch	W	<input type="checkbox"/> S768-6W*		

* Not cULus Listed & NOM certified

Porcelain Ceiling Lampholders



Rating		Description	Color	Catalog No.	
W	V/AC				
660	125	Two Piece, w/ 15A 125V/AC 2P 2W Outlet, 2 Screw Terminals, Top Wire, Pull Chain Switch	W	<input type="checkbox"/> 669	
		Two Piece, w/ 15A 125V/AC 2P 3W Outlet, 2 Screw Terminals, Top Wire, Pull Chain Switch	W	<input type="checkbox"/> 667	
660	250	One Piece, w/ Feed-Through, 4 Screw Terminals, Top Wire, Keyless Switch	W	<input type="checkbox"/> 604	
		Two Piece, w/ Feed-Through, 4 Screw Terminals, Top Wire, Pull Chain Switch	W	<input type="checkbox"/> 659	



S788W



S1174W



669



604

Color Information:

W (White)



(White)

Specifications and availability are subject to change without notice.

Indicates NAFTA Compliant - Page R-30